


Heyco® PG Threaded Plugs

Round Head with Slot

THREAD TYPE/SIZE	PART NO.		DESCRIPTION	PART DIMENSIONS			
	Gray	NEW! Black		A Head Diameter		B Overall Height	
				in.	mm.	in.	mm.
PG 7	3405	3405B	TP PG 7	.59	15,0	.32	8,0
PG 9	3407	3407B	TP PG 9	.75	19,0	.37	9,5
PG 11	3402	3402B	TP PG 11	.87	22,0		
PG 13	3412	3412B	TP PG 13	.98	25,0	.39	10,0
PG 16	3414	3414B	TP PG 16	1.06	27,0		
PG 21	3416	3416B	TP PG 21	1.30	33,0	.47	12,0
PG 29	3418	3418B	TP PG 29	1.73	44,0		
PG 36	3415	3415B	TP PG 36	2.17	55,0	.55	14,0
PG 48	3417	3417B	TP PG 48	2.72	69,0	.63	16,0

Standard color gray. Consult Heyco for black and other colors.



- Used to close unneeded PG and Metric threaded holes when other threaded accessories may be added at a later time.
- Protection Class IP 50.
- PG plugs are molded of shock resistant polystyrene and metric plugs are molded of Nylon 6.
- Designed with slot for screwdriver installation.
- For PG Thread specifications, see page 3-37 in Heyco's Catalog 113
- Working temperature range: -4°F (-20°C) to 176°F (80°C).
- Consult Heyco for other colors.


Heyco® Metric Threaded Plugs

Round Head with Slot

THREAD TYPE/SIZE	PART NO.		DESCRIPTION	PART DIMENSIONS			
	Gray	NEW! Black		A Head Diameter		B Overall Height	
				in.	mm.	in.	mm.
M12 x 1,5	3403	3403B	TP M12	.59	15,0		
M16 x 1,5	3404	3404B	TP M16	.79	20,0	.41	10,5
M20 x 1,5	3406	3406B	TP M20	.95	24,0		
M25 x 1,5	3408	3408B	TP M25	1.18	30,0	.51	13,0
M32 x 1,5	3409	3409B	TP M32	1.48	37,0	.53	13,5
M40 x 1,5	3410	3410B	TP M40	1.81	46,0	.55	14,0
M50 x 1,5	3411	3411B	TP M50	2.17	55,0	.63	16,0
M63 x 1,5	3413	3413B	TP M63	2.76	70,0	.71	18,0

Standard color gray. Consult Heyco for black and other colors.

- For Heyco Snap-In Metric Dome Plugs, see page 9.



Materials	PG	Shock Resistant Polystyrene
Flammability Rating	Metric	Nylon 6
Temperature Rating		94V-2
IP Rating		-4°F (-20°C) to 176°F (80°C)
		IP 50

*Quick
Specs*

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[3402](#) [3403](#) [3404](#) [3405](#) [3406](#) [3407](#) [3408](#) [3409](#) [3410](#) [3411](#) [3412](#) [3413](#) [3414](#) [3415](#) [3416](#) [3417](#) [3418](#) [3401](#)