


REV	DOCUMENT	CHANGED BY	CHECK
A	0038847	PK 11APR08	ASD



1. TERMINALS WILL ACCEPT 6.35mm WIDE QUICK CONNECT RECEPTACLES AND COMPLY WITH EN61058-1 REQUIREMENTS.

CHARACTERISTICS		ELECTRICAL DATA		DESIGN UNITS: MM		DRAWN		KSR		07APR08		Honeywell									
CONTACT ARRANGEMENT		 16(4)A 250V~ 25T125 μ 5E4  16A 1/2HP 125/250VAC		TOLERANCES UNLESS NOTED:		CHECK		RJ		07APR08						TITLE SWITCH - BASIC					
S.P.N.C				NO PLACE X ± ±		ONE PLACE .X ± ±		TWO PLACE .XX ± ± 0.40		THREE PLACE .XXX ± ±										ANGLES X ± ± 2°	
OPERATING FORCE: 100gf MAX.				THIRD ANGLE PROJECTION				AutoCAD		SCALE		NTS		SHEET		1 OF 1					
DIFFERENTIAL FORCE:												SIZE		TYPE		CAGE CODE		DRAWING NAME		REV	
RELEASE FORCE: 25gf MIN.												B		I				V15T16-CC100		A	
FREE POSITION:																					
OPERATING POSITION: 14.7±0.5MM.																					
PRE-TRAVEL: 1.6MM MAX.																					
DIFFERENTIAL TRAVEL: 0.4MM MAX.																					
OVER-TRAVEL: 0.8MM MIN.																					
FULL OVERTRAVEL FORCE:																					