




- Surface Mount Package
- Robust Construction for IR Processes
- Operating Temperature : 0°C to 85°C


Electrical Parameters @ 25° C

Inductance (μ H Typ.)	DCR (Ω Max.)	Hipot (Vrms)	CMRR
@100 KHz, 100 m Vrms			
5.0	0.250	300	See Graph
Pins 1-8, 2-7, 3-6 and 4-5	Pins 1-8, 2-7, 3-6 and 4-5		


Schematic



Typical CMRR



Package



Unless Otherwise Specified Dimensions are in Inches /mm $\pm .010 / .25$