



SCREWDRIVERS/BITS



www.eclipsetools.com

Screwdriver-Rubber Grip

- These Cushion-Grip screwdrivers offer excellent comfort and durability. Our grips are designed to allow repetitive use with little or no fatigue.
- The Cushion-Grip is fitted onto a hard plastic core for strength.
- The rubberized outer grip feels good in the hand, yet still transfers torque effectively.
- The screwdriver blade portion that is inside the hard plastic core has protruding tabs formed on it to maintain a secure fit to the handle and superior torque performance.



Flat Blade



Description	Part No.
Screwdriver - Rubber Grip (13/64" x 3")	800-097
Screwdriver - Rubber Grip (13/64" x 4")	800-099
Screwdriver - Rubber Grip (13/64" x 6")	800-095
Screwdriver - Rubber Grip (1/4" x 1-1/2")	800-101
Screwdriver - Rubber Grip (1/4" x 4")	800-093



Phillips



Description	Part No.
Screwdriver - Rubber Grip (#1 x 3")	800-098
Screwdriver - Rubber Grip (#1 x 4")	800-100
Screwdriver - Rubber Grip (#2 x 1-1/2")	800-102
Screwdriver - Rubber Grip (#2 x 4")	800-094
Screwdriver - Rubber Grip (#2 x 6")	800-103
Screwdriver - Rubber Grip (#2 x 8")	800-096
Screwdriver - Rubber Grip (#2 x 10")	800-104

Screwdriver-Rubber Grip-Offset Speed Driver



Description	Part No.
Offset Screwdriver (Phillips: #1) W/Cushion Grip	800-089
Offset Screwdriver (Slotted: 13/64") W/Cushion Grip	800-090



Robertson (Square) Tip



Description	Part No.
Screwdriver - Rubber Grip (S0 x 4")	800-105
Screwdriver - Rubber Grip (S1 x 4")	800-106
Screwdriver - Rubber Grip (S2 x 4")	800-107
Screwdriver - Rubber Grip (S3 x 4")	800-108

Screwdriver-Rubber Grip



Star Tip



Description	Part No.
Star Screwdriver - Rubber Grip (T45) Star Tip	800-109
Star Screwdriver - Rubber Grip (T20) Star Tip	800-110
Star Screwdriver - Rubber Grip (T25) Star Tip	800-111
Star Screwdriver - Rubber Grip (T27) Star Tip	800-112
Star Screwdriver - Rubber Grip (T30) Star Tip	800-113



Hollow Shaft Nutdrivers



Precision-machined socket




All-hollow shaft

Now available separately

Description	Part No.
7 Pc Set with Roll-up Pouch	800-088
Hollow-Shaft Nutdriver (3/16")	902-231
Hollow-Shaft Nutdriver (1/4")	902-232
Hollow-Shaft Nutdriver (5/16")	902-233
Hollow-Shaft Nutdriver (11/32")	902-234
Hollow-Shaft Nutdriver (3/8")	902-235
Hollow-Shaft Nutdriver (7/16")	902-236
Hollow-Shaft Nutdriver (1/2")	902-237

Screwdriver



Screwdriver



Description	Tip	Working length	Part No.
Screwdriver	# 000	2"	800-131
Screwdriver	# 00	2"	800-132
Screwdriver	# 0	3"	800-133
Screwdriver	# 1	6"	800-134



Screwdriver



Description	Tip	Working length	Part No.
Screwdriver	1.0	2"	800-135
Screwdriver	1.6	2"	800-136
Screwdriver	2.0	2"	800-137
Screwdriver	2.4	3"	800-138
Screwdriver	3.0	4"	800-139



Screwdriver



Description	Tip	Working length	Part No.
Screwdriver	T10H	2"	800-140
Screwdriver	T3	2"	800-141
Screwdriver	T4	2"	800-142
Screwdriver	T5H	2"	800-143
Screwdriver	T6H	2"	800-144
Screwdriver	T7H	2"	800-145
Screwdriver	T8H	2"	800-146
Screwdriver	T9H	2"	800-147

Screwdriver set




Description	Part No.
Screwdriver set	800-149

Screwdriver set




Description	Part No.
Screwdriver set	800-150

Ceramic Driver



Description	Part No.
0.015" x 0.035" (0.4x0.9mm)	800-114
0.015" x 0.047" (0.4x1.2mm)	800-115
0.015" x 0.055" (0.4x1.4mm)	800-116
0.015" x 0.070" (0.4x1.8mm)	800-117
0.015" x 0.078" (0.4x2.0mm)	800-118
0.015" x 0.094" (0.4x2.4mm)	800-119
0.027" x 0.094" (0.7x2.4mm)	800-120
PHO	800-121
PH1.7	800-122

ESD Precision Screwdriver



ESD-Safe for maximum protection of static electricity sensitive components.

Model No.	Spec.
SD-083-P2	#00
SD-083-P3	#0
SD-083-P4	#1
SD-083-S3	2.0
SD-083-S4	2.4
SD-083-S5	3.0
SD-083-T4	T4
SD-083-T5H	T5H
SD-083-T6H	T6H

ESD Precision Screwdriver Set





Contents	
SD-083-P2	#00
SD-083-P3	#0
SD-083-P4	#1
SD-083-S3	2.0
SD-083-S4	2.4
SD-083-S5	3.0
SD-083-T4	T4
SD-083-T5H	T5H
SD-083-T6H	T6H

Description	Part No.
ESD Precision Screwdriver Set	SD-0839



Soft-Handled Screwdrivers



- Rubber grip
- Ergonomic design
- Chrome vanadium blades
- Hardened, tempered, Black-oxide tip

Display Stand (Distributors only)



- For distributors
- Each size holds 50 screwdrivers
- Great for displaying our product

Description	Part No.
Small Stand	900-031
Large Stand	900-014

11 Pc Star Screwdriver Set



- T6 thru T40
- Same handle as our popular screwdriver line
- Convenient plastic carrying case

Description	Part No.
11 PC Star Screwdriver Set	800-030

Description (Inch)						Part No.
A	Tip	B	C	D	E	
3	⊖	1/8	3.3	1/8	6.3	800-001
3	⊕	#0	3.3	1/8	6.3	800-002
4	⊖	1/8	3.3	1/8	7.3	800-010
4	⊕	#0	3.3	1/8	7.3	800-011
6	⊖	1/8	3.3	1/8	9.3	800-012
6	⊕	#0	3.3	1/8	9.3	800-013
3	⊖	3/16	4.3	3/16	7.3	800-003
3	⊕	#1	4.3	3/16	7.3	800-004
4	⊖	3/16	4.3	3/16	8.3	800-014
4	⊕	#1	4.3	3/16	8.3	800-015
6	⊖	3/16	4.3	3/16	10.3	800-016
6	⊕	#1	4.3	3/16	10.3	800-017
8	⊖	3/16	4.3	3/16	12.3	800-018
8	⊕	#1	4.3	3/16	12.3	800-019
10	⊖	3/16	4.3	3/16	14.3	800-020
10	⊕	#1	4.3	3/16	14.3	800-021
4	⊖	1/4	4.3	1/4	8.3	800-005
4	⊕	#2	4.3	1/4	8.3	800-006
6	⊖	1/4	4.3	1/4	10.3	800-022
6	⊕	#2	4.3	1/4	10.3	800-023
8	⊖	1/4	4.3	1/4	12.3	800-024
8	⊕	#2	4.3	1/4	12.3	800-025
10	⊖	1/4	4.3	1/4	14.3	800-026
10	⊕	#2	4.3	1/4	14.3	800-027
Stubby	⊖	1/4	0.7	1/4	3	800-028
Stubby	⊕	#2	0.7	1/4	3	800-029
2	⊕	T05	3.3	5/32	5.3	800-032
2	⊕	T06	3.3	5/32	5.3	800-033
2	⊕	T07	3.3	5/32	5.3	800-034
3	⊕	T08	3.3	5/32	6.3	800-035
3	⊕	T09	3.3	5/32	6.3	800-036
3	⊕	T10	3.3	5/32	6.3	800-037
3	⊕	T15	3.3	5/32	6.3	800-038
2	⊕	T07	3.3	5/32	5.3	800-043
3	⊕	T08	3.3	5/32	6.3	800-044
3	⊕	T09	3.3	5/32	6.3	800-045
3	⊕	T10	3.3	5/32	6.3	800-046
3	⊕	T15	3.3	5/32	6.3	800-047
2	⊕	TR1	3.3	1/8	5.3	800-123

2-in-1 Ceramic Drivers



Description			Part No.
Material	Type(Inch)	OAL(Inch)	
Bit: Zirconia Body: ABS ABS (fireproof)	A 0.4 X 0.035	5.39	902-191
	B 0.4 X 0.07		
	A 0.4 X 0.047		902-192
	B 0.4 X 0.078		
	A 0.4 X 0.047		902-194
	B 0.4 X 0.094		
	A 0.4 X 0.047		902-195
	B PH1.7		
	A 0.4 X 0.035		902-196
	B PHO		

5 Pc Reversible Ceramic Driver Set

- Contains: 5 pen style drivers with 2 reversible tips in each
- Straight and phillips tips of various sizes


Description	Part No.
5 Pc Reversible Ceramic Driver Set	800-062



Pro-soft Screwdriver Set



- 3.2x2-15/16"
- 5x2-15/16"
- 6x3-15/16"
- #0x2-15/16"
- #1x2-15/16"
- #2x3-15/16"




Description	Part No.
Pro-soft Screwdriver Set	902-096

Pro-soft Screwdriver Set



- T5Hx1-15/16"
- T6Hx1-15/16"
- T7Hx1-15/16"
- T8Hx1-15/16"
- T9Hx1-15/16"
- T10Hx1-15/16"
- T15Hx2-15/16"



Description	Part No.
Pro-soft Screwdriver Set	902-097


6 Pc Precision Screwdriver Set



- #0 X 3", #1 X 4", #1 X 6" Phillips
- .10x3", .12 x 4", .15x6" Flat Blade

Description	Part No.
6 Pc Precision Screwdriver Set	800-007


6 Pc Electronic Screwdriver Set



- Includes standup rack
- #0-3 x 1.6", #0-2 x 3", #0 x 3" phillips
- .08 x 1.6", .10 x 3", .12 x 3" straight blade

Description	Part No.
6 Pc Electronic Screwdriver Set	800-009

6 Pc Precision Screwdriver Set with Cutter



- Micro cutter, spring loaded
- 6 pc Swivel cap Screwdrivers
- .10x3", .12x4", .16x6" Flat
- #00x3", #0x4", #1x6" Phillips

Description	Part No.
6 Pc Precision Screwdriver Set with Cutter	800-077

7 Pc Precision Screwdriver

- 2" blade length
- Cupped Swivel cap
- 4 Flat blade- 1.6, 2.0, 2.4, 3.0mm
- 3 Phillips-#00, #0, #1



Description	Part No.
7 Pc Precision Screwdriver	800-075

15 Pc Precision Screwdriver Set

- Color coded handles for different types
- 4 pc Yellow Hex - 1.5, 2.0, 2.5 & 3.0 mm
- 4 pc Green Slotted - 1.0, 2.0, 3.0 & 3.5 mm
- 4 pc Blue Star Tip - T6, T8, T10 & T15
- 3 Pc Red Phillips - #000, #00 and #0
- Molded Case with fitted pockets for storage



Description	Part No.
15 Pc Precision Screwdriver Set	800-073

20 Pc Precision Electronic Screwdriver Set

- One handle with interchangeable bits
- #00 and #0 Phillips, 2.0, 2.5, 3.0, 4.0 mm straight blades
- T-6, 7, 8, 9 & 10 star bit, 1.5, 2.0, 2.5 mm hex
- Pozidrive #0 and #00



Description	Part No.
20 Pc Precision Electronic Screwdriver Set	800-060

Folding Security Star Tip

- T9 - T40 security Star Tip
- Chrome plated keys
- Green lacquered case



Description	Part No.
Folding Security Star Tip	800-052

7 Pc Folding Hex Set



Description	Part No.
7 Pc Folding Hex Set (1/16", 5/64", 3/32", 1/8", 5/32", 3/16" & 1/4")	800-066
7 Pc Folding Hex-Metric (1.5, 2, 2.5, 3, 4, 5, 6mm)	800-124

9 Pc Ball Point Hex Wrench Set



- 1/16", 5/64", 3/32", 1/8", 5/32", 3/16", 1/4", 5/16" & 3/8"
- Mirror polished
- Long arm type
- Ball point allows for slightly indirect operation

Description	Part No.
9 Pc Ball Point Hex Wrench Set	800-065
9 Pc Long Arm Hex - Metric	800-125

30 Pc Hex Key Set



- Inch side .028 to 3/8"
- Metric side 0.9 to 10mm
- 15-Pc inch size
- 15-Pc metric size
- Handy plastic

Description	Part No.
30 Pc Hex Key Set	900-038

Folding Key Set




- Material: SAE6150 Chrome vanadium steel
- Case: T.P.R. Anti-slip
- Key: Satin finish

Description	Part No.
8 PC Folding Security Star Key Set(T9H, T10H, T15H, T20H, T25H,T27H, T30H, T40H)	902-100
9 PC Folding Hex Key Set(3/16",7/32",1/4",5/32",9/64",1/8",7/64",3/32", 5/64")	902-226

16 Pc Hex Key Wrench Set

Pocket size designed for various uses.



Part No.	Tip size	S	L
902-101(inch)	1/16"	14	46
	5/64"	17	48
	3/32"	17	52
	1/8"	20	58
	5/32"	22	65
	3/16"	25	72
	7/32"	28	77
	1/4"	29	86

Allen key reference table

Hex wrench (mm)	0.71	0.89	1.27	1.5	1.6	2	2.4	2.5	3	3.2	4	5	6	8	10	12
Hexagonal head bolts			M1.4	M1.6/M2	M2	M2.5	M3	M3	M4	M4	M5	M6	M8	M10	M12	M14
Hexagonal head set screws	M1.6/M1.7	M2	M2.5	M3		M4	M5	M6	M8	M10	M12	M16	M20	M22		

Description	Part No.
16 PC Hex Key Wrench Set	902-101


Double-ended Screwdriver



- Pocket clip
- Straight blade on long end
- Phillips on short end

Description	Part No.
Double-ended Screwdriver	800-040

Pocket Clip Screwdriver



Description	Part No.
1/8" Straight blade	800-041
#0 Phillips blade	800-042


4-in-1 Screwdriver

- Two Double-Ended, Reversible Tips



Description	Part No.
4-in-1 Screwdriver-Pen Style	800-092
4-in-1 Screwdriver-Pen Style (50 pc Display Box)	800-092-50

6-In-1 Magnetic Quick Change Screwdriver



- Industrial quality with maximum versatility. Shock proof acetate handle and S2 alloy steel bit.
- OAL: 7"

Description	Part No.
6-In-1 Magnetic Quick Change Screwdriver	800-080

Magnetizer/Demagnetizer



- High-impact casing
- Magnetize/demagnetize screwdrivers/tweezers and other small tools

Description	Part No.
Magnetizer/Demagnetizer	800-070

Can Wrench



- Popular Telecom tool
- 3/8" and 7/16" hex ends
- Insulated body

Description	Part No.
Can Wrench	900-055


CATV Install/Extract Tool



- Installs and removes F-Type connectors in hard to reach places
- Handle contains male F-Type holder

Description	Part No.
CATV Install/Extract Tool 12" (shown)	800-072
CATV Install/Extract Tool 6"	800-079


BNC Connector Insertion / Removal Tool



- Provides easy access to difficult to reach, high density connectors


Description	Part No.
12 inch (shown)	800-050
8 inch	800-049

Double-end Reversible Screwdriver



Description	Part No.
Double-end Reversible Screwdriver	800-148

1/2" T-handle Hex Hey



Description	Part No.
1/2" T-handle Hex Hey	HW-928

10 Pc T-Handle Hex Key Set

- 3/32", 7/64", 1/8", 9/64", 5/32", 3/16", 7/32", 1/4", 5/16", 3/8"



Description	Part No.
10 PC T-Handle Hex Key Set	800-067

7 Pc T-Handle Hex Hey Set

- Long reach design with T-handle for greater torque and ease of use
- Hardened S2 steel alloy
- Set comes in a durable blow-molded case
- 3/32", 1/8", 5/32", 3/16", 1/4", 5/16" and 3/8"



Description	Part No.
7 PC T-Handle Hex Hey Set	800-091

Screwholding Screwdriver Set



- Contents:
- 0.2 x 6.1, 0.2 x 5.1, 0.1 x 5.1
- #1 0.2 x 5.1, #2 0.2 x 7.1

Description	Part No.
Screwholding Screwdriver - Set	800-151

3 Pc Anti-Static Alignment Set



- For protection of sensitive components
- Duplex, trimmer and square/hex tool
- Conductive nylon-avoid high voltage

Description	Part No.
3 PC Anti-Static Alignment Set	800-130

Bit Set**Item #: 800-128****Item #: 800-127**

Description	Part No.
18 Pc Bit Set (Clips to belt)	800-127
20 Pc Bit Set (Clips to belt)	800-128


20-in-1 Telescoping, Magnetic Screwdriver**Opened**

- Self contained Bits and Sockets
- Magnetic telescoping tip to hold bits and screws
- 13 piece bits
- 5 piece sockets

Description	Part No.
20-in-1 Telescoping, Magnetic Screwdriver	800-039

Star Wrench Driver Set


T-8 to T-30 have tamper proof holes for preventing tampering for cordless telephones and wireless equipment.



Design with tips at both ends for horizontal and vertical use.



Description	Part No.
Star Wrench Driver Set	902-069

Flexible, Ratcheted Screwdriver Set

- 7.5" flexible shaft
- Good for getting into hard to reach areas
- 10 pc Bit set

Description	Part No.
Flexible, Ratcheted Screwdriver Set	800-076

Twin Wrench/Driver Set

- Tips at both ends for vertical or horizontal use
- T10, T15, T20 Star Tip bits
- 3 Flat blade screwdriver bits
- 4 Phillips screwdriver bits


Description	Part No.
Twin Wrench/Driver Set	800-068

17 Pc Offset Ratchet & Socket Driver Set

- Offset ratchet handle, reversible
- 6 pc socket set, 1/4" hex drive
- 10 pc 1/4" hex screwdriver bits

Description	Part No.
17 PC Offset Ratchet & Socket Driver Set	800-078

33 Pc Security Bit Pack



- Security bit assortment
- 8 piece security hex
- 12 piece security Torx
- 4 piece security spanner
- 4 piece tri-wing
- 4 piece phillips
- 1/4" magnetic bit holder
- Honeycomb plastic case

Description	Part No.
33 PC Security Bit Pack (S2 grade steel) Superior grade	800-048
33 PC Security Bit Pack (SAE 6150 CR-V steel) Economy grade	800-048E

Ratcheted Screwdriver Handle



- Ratcheting
- Swiveling
- Reversible
- Heavy-duty rubber grip
- Your bits can be stored in handle holder

Description	Part No.
Ratcheted Screwdriver Handle	800-074

22 Pc 1/4" Drive Socket Set



- 1/4" Ratchet
- 9 pc Inch 3/16" to 1/2"
- 9 pc metric 4mm to 12mm
- 3" and 6" extensions
- Nutdriver handle

Description	Part No.
22 Pc 1/4" Drive Socket Set	900-194

All-In-One Tool Set



- Contains: 9 SAE sockets, 9 metric sockets, 21 screwdriver bits, 5 drill bits, needle-nosed pliers, 6" adjustable wrench, reversible ratchet screwdriver handle, flexible extension, magnetic bit holder, socket adaptor

Description	Part No.
All-In-One Tool Set	800-061

58-piece Precision Electronic Screwdriver Set

Features:

- Material: Chrome-Molybdenum Vanadium Steel Bits 56 pcs, Length: 1.1 inch
- Ergonomic, double molded structure. Non-slip.
- Light weight designed (10 ounces)



With-magnetic

Contents	
+	#000, #00, #0, #1
-	1.0mm, 1.5mm, 2.0mm, 2.5mm, 3.0mm, 3.5mm, 4.0mm
⚙	T5H, T6H, T7H, T8H, T9H, T10H, T15H, T20H
⚙	T3, T4, T5, T6, T7, T8, T9, T10, T15
⚙	1.5mm, 2mm, 2.5mm, 3mm, 1/16", 5/64", 3/32"
⚙	2mm, 2.3mm, 2.5mm
⚙	0.7mm, 0.9mm, 1.3mm, 1.5mm, 2mm, 2.5mm, 3mm, 4mm, 0.028", 0.035", 0.05", 1/16", 5/64", 3/32"
⚙	#0, #1
⚙	TR1
⚙	2mm

Description	Part No.
58-piece Precision Electronic Screwdriver Set	902-219

Ratcheted Screwdriver Set of 10 bits(double ended)



Description	Part No.
Ratcheted Screwdriver Set of 10 bits (double ended)	800-051


11 Pc Cellular Phone Maintenance Tool Kit

Supplied with T-Grip holder, slotted tip 0.5mm X 2.0mm, T5, T6, T8, Phillips #1, pressing blade, panel pry bar, spanner 5mm, and antenna repair tool. It's ideal for the repair and maintenance of cellular phones.



Description	Part No.
11 PC Cellular Phone Maintenance Tool Kit	902-222

Pro-soft Spanner Security Screwdriver Set




Unit: inch

Description	Pro-soft Spanner Security Screwdriver Set						
Part No.	A	B	C	D	E	G	H
902-098	.02	.02	.16	.08	.39	3.15	3.35
	.04	.02	.20	.08	.39	3.15	4.33
	.04	.02	.20	.09	.39	3.15	4.33
	.05	.02	.21	.10	.39	3.15	4.33
Contents	M1.7, M2.0, M2.3, M2.6						



14 Pc Ratchet Precision Screwdriver Set



Description	Part No.
14 PC Ratchet Precision Screwdriver Set	SD-9312

33 Pc Screwdriver Set w/Bits

Bits Contents:

- ⊕ PH000x1.1
- ⊕ PH00x1.1
- ⊕ PH0x1.1
- ⊕ PH1x1.1
- ⊖ SL1.0x1.1
- ⊖ SL1.5x1.1
- ⊖ SL2.0x1.1
- ⊖ SL2.5x1.1
- ⊖ SL3.0x1.1
- ⊖ SL3.5x1.1
- ⊖ SL4.0x1.1
- ⊕ T4x28
- ⊕ T5x28
- ⊕ T6x28
- ⊕ T7x28
- ⊕ T8x1.1
- ⊕ T9x1.1
- ⊕ T10x1.1
- ⊕ T15x1.1
- ⊕ T20x1.1
- ⊕ H0.7x1.1
- ⊕ H0.9x1.1
- ⊕ H1.3x1.1
- ⊕ H1.5x1.1
- ⊕ H2.0x1.1
- ⊕ H2.5x1.1
- ⊕ H3.0x1.1
- ⊕ H4.0x1.1
- ⊕ PZ1x1.1
- ⊕ PZ0x1.1

Socket:

- ⊖ M5
- ⊖ M6

Shaft:

- ⊖ M4



Description	Part No.
33 PC Screwdriver Set w/Bits	800-129

6 Pc Insulated Precision Screwdriver Set

- Provides Shock Protection to 1000V AC
- Meet VDE Standards for safety to 1000V AC
- Both sets come complete with a plastic storage case
- Material (Blade): Cr-Mo
- OAL: 6-4/16 inches



1000V 04


- ⊖ 0.4x2.0x2-9/16"
- ⊖ 0.4x2.5x2-9/16"
- ⊖ 0.23x1.5x2-9/16"
- ⊕ PH0x2-9/16"
- ⊕ PH00x2-9/16"
- ⊕ PH1x2-9/16"



Description	Part No.
6 PC Insulated Precision Screwdriver Set	902-099

30-Piece Do-It-All Kit

This comprehensive kit will work with almost every type of fastener.



Contents	
	SQ1, SQ2
	PH0, PH1, PH2, PH3
	PZ0, PZ1, PZ2, PZ3
	SL3.5, 4.5, 5.5, 6, 8
	HX2, 2.5, 3, 4, 5, 6, 8
	T5, T6, T7, T8, T10, T15, T20, T35

Description	Part No.
30-Piece Do-It-All Kit	SD-2313

5-in-1 Screwdriver with LED Flashlight

#0 1/8" #00 1/16"



50 pcs display pack

Description	Part No.
5-in-1 Screwdriver with LED Flashlight (50 Pcs display pack)	SD-804
5-in-1 LED Screwdriver Single pc	SD-804-1

12 Pc Pro-Soft Screwdriver Set




Contents	
	2.0x50
	3.0x75
	5.0x75
	6.0x40
	6.0x100
	6.0x200
	#00x50
	#0x75
	#1x75
	#2x40
	#2x100
	#2x200

Comes in a plastic molded tray!

Description	Part No.
12 Pc Pro-Soft Screwdriver Set	SD-2312

10 Pc Pro-Soft Screwdriver Set

Mobile telephone, communication equipment, radio and precision equipment.




Spec.	
#000	
#00	
1.0	
1.6	
2.0	
T3	
T4	
T5H	
T6H	
T7H	

Description	Part No.
10 Pc Pro-Soft Screwdriver Set	SD-9810

62 Pc Security Bit Set

- Contents:
- M5, M6, M8
- C1, C2, C3
- 1/8", 3/16"
- 2mm x 2mm x 2mm
- S0, S1, S2, S3
- 1, 2, 3, 4, 5
- 0, 1, 2
- Wing nut driver
- 6, 8, 10
- PZ0, PZ1, PZ2
- 4, 6, 8, 10, 12
- T-5, T-6, T-7, T-8, T-10, T-15, T-20, T-25, T-27, T-30, T-40
- 2mm, 2.5mm, 3mm, 4mm, 5mm, 6mm, 8mm, 5/64", 3/32", 7/64", 1/8", 9/64", 5/32"
- 1 Pc 1/4" x 60mm magnetic bits holder
- 1 Pc bits holder socket
- 1 Pc socket adapter
- 1 Pc ratchet screwdriver



Description	Part No.
62 Pc Security Bit Set	800-081

21 Pc 1/4" & 3/8" Dual Function Ratchet Handle Sockets Set



- Handy, all-in-one 21-piece ratchet set!
- Chrome vanadium steel bits.
- Includes a custom storage case.
- Light weight design, 1063g per set.
- 18 bits with one stubby ratchet handle, and two extension bars.

Description	Part No.
21 Pc 1/4" & 3/8" Dual Function Ratchet Handle Sockets Set	SD-2306M

Contents
1 pc 1/4" DR & 3/8" DR stubby ratchet handle
1 pc extension bar 1/4" DR x2"
1 pc extension bar 3/8" DR x3"
8 pc 3/8" DR socket: 10mm, 11mm, 12mm, 13mm, 14mm, 15mm, 17mm, 19mm
10 pc 1/4" DR socket: 4mm, 5mm, 6mm, 7mm, 8mm, 9mm, 10mm, 11mm, 12mm, 13mm

35 Pc 1/4" Drive Socket & Screwdriver



- Featuring ratchet lock function, and two unique handles for more flexible work.
- Handy, all-in-one 35-piece ratchet set!
- Chrome vanadium steel bits.
- Includes a custom storage case.
- Light weight design, 679g per set.

Description	Part No.
35 Pc 1/4" DR Socket & Screwdriver	SD-2307M

Contents
11 pc 1/4" DR sockets: 4mm, 5mm, 5.5mm, 6mm, 7mm, 8mm, 9mm, 10mm, 11mm, 12mm, 13mm
20 pc bits: PH0, PH1, PH2, PH3 T10, T15, T20, T25, T30, T40 3mm, 5mm, 7mm PZ2 2.5mm, 3mm, 4mm, 5mm, 6mm, 8mm
1 pc ratchet handle 1/4" DR
1 pc bit holder
1 pc handle driver
1 pc 1/4" x 2" ext bar

35 Pc 1/4" Drive Socket & Screwdriver W/Long Nosed Plier Set

- Featuring ratchet lock function, universal joint, and adjustable T-bar.
- Chrome vanadium steel bits.
- Light weight design, 908g per set.
- Handy, all-in-one 35-piece variety of tools!
- Includes a patented reversible storage case.

Contents	
11 pc 1/4" DR sockets: 4mm, 5mm, 5.5mm, 6mm, 7mm, 8mm, 9mm, 10mm, 11mm, 12mm, 13mm	
12 pc bits: ⊕ PH1, PH2, PH3 ⊗ T10, T15, T20, T25, T30 ⊖ 3mm, 4mm, 5mm, 6mm	
4 pc 50mm bit ⊕ PH2, PH3 ⊖ 6mm, 7mm	
2 pc ext bar 1/4"x3" ,1/4"x6"	1 pc long nose plier (135mm)
1 pc ratchet handle	1 pc 1/4" DR adjustable T-bar
1 pc bit holder	1 pc handle driver
1 pc 1/4" x 1/4" universal joint	




Double-sided design reversible storage case.

Description	Part No.
35 Pc 1/4" DR Socket & Screwdriver W/Long Nose Plier Set	SD-2308M

40 Pc Reversible Ratchet Screwdriver W/Bits & Sockets Set

- Handy, all-in-one 40-piece ratchet set!
- Featuring dual-color rotatable ratchet handle.
- Chrome vanadium steel bits.
- Includes a custom storage case.
- Light weight design, 733g per set.

Contents	
11 pc 1/4" DR sockets: 4mm, 5mm, 5.5mm, 6mm, 7mm, 8mm, 9mm, 10mm, 11mm, 12mm, 13mm	
26 pc bits: ⊕ PH0, PH1, PH2, PH3 ⊗ T10, T15, T20, T25, T30, T40 ⊖ 3mm, 4mm, 5mm, 6mm, 8mm ⊗ PZ0, PZ1, PZ2, PZ3 ⊙ 2mm, 2.5mm, 3mm, 4mm, 5mm, 6mm, 7mm	
1 pc adapter	
1 pc magnetic bit holder 100mm	
1 pc 3-position reversible ratchet screwdriver	



Description	Part No.
40 Pc Reversible Ratchet Screwdriver W/Bits & Sockets Set	SD-2309

100 Pc Assorted Power Bits Set

- Handy, all-in-one 100-piece ratchet set!
- Includes a custom storage case.
- Chrome vanadium steel bits.
- Light weight design, 669g per set.

Contents	
96 pc bits: ⊕ PH1, PH2 ⊕ S2: PH0, PH1, PH2, PH3 ⊖ C1, C2, C3 ⊕ S0, S1, S2, S3 ⊙ 1, 2, 3, 4, 5 ⊕ 6, 8, 10 ⊗ PZ0, PZ1, PZ2, PZ3 ⊕ 2mm x 2mm x 2mm ⊙ M5, M6, M8 ⊖ 2mm, 3mm, 5mm ⊙ 4, 6, 8, 10, 12 ⊕ Wing nut driver ⊙ 1.5mm, 2mm, 2.5mm, 3mm, 4mm, 4.5mm, 5mm, 5.5mm, 6mm, 7mm, 8mm, 1/16", 5/64", 3/32", 7/64", 1/8", 9/64", 5/32", 3/16", 7/32", 1/4" ⊙ 2mm, 3mm, 4mm, 5mm, 6mm, 7mm, 8mm, 5/64", 3/32", 7/64", 1/8", 9/64", 5/32", 3/16", 7/32", 1/4" ⊗ T5H, T6H, T8H, T10H, T15H, T20H, T25H, T27H, T30H, T35H, T40H ⊗ T5, T6, T8, T10, T15, T20, T25, T27, T30, T40	
1 pc sockets adapter	1 pc dry wall stopper
1 pc bits holder	1 pc magnetic bit holder



Description	Part No.
100 Pc Assorted Power Bits Set	SD-2310