



BU-00000-★
Part # color

★ 0 - Black 5 - Green
2 - Red 6 - Blue
4 - Yellow 9 - White

CLIPS & INSULATORS



[Enlarge](#)

BU-60U Alligator Clip - 10 Amp

- Steel, standard clip with out barrel construction
- Solder or crimp connection
- 5/16" (7.9mm) max. jaw opening
- Nose width 0.13"
- [Product Data Sheet](#)
- [Send us your questions about this product](#)

Alligator Clip with Screw - 10 Amp:

BU-60S (Steel)

BU-60CS (Solid Copper)

- A 640 screw eliminates soldering or crimping
- Nose width 0.13"
- Federal spec.: Type TC-I W-C-440B (BU-60CS)
- [Product Data Sheet](#)
- [Send us your questions about this product](#)



[Enlarge](#)



[Enlarge](#)

BU-60PR2 Phone Tip Alligator Clip - 10 Amp

- Barrel construction accepts standard phone tip or test prod tip
- Barrel diameter 0.075" (1.9mm) ID
- Nose width 0.13"
- Steel
- [Product Data Sheet](#)
- [Send us your questions about this product](#)

BU-60HPR-★ Phone Tip Alligator Clip with Acetate Handle - 10 Amp

- Barrel construction accepts standard phone tip or test prod tip
- Barrel diameter 0.075" (1.9mm) ID
- Nose width 0.13"
- Steel
- Available in black, red, yellow, green, blue and white
-
-
- [Product Data Sheet](#)
- [Send us your questions about this product](#)



[Enlarge](#)

[Insulated BNCs](#) | [Test Leads](#) | [Insulated Test Accessories](#)
[Accessories & Probes](#) | [Kits](#) | [Cross Reference](#)

© 2003 Mueller Electric Company. All rights reserved.
Problems with the site should be reported to the [webmaster](#).