

64328 HLX-Z/C 65-15

Halogen lamps, current-controlled with PK30d base



- Airfield lighting

Product benefits

- Reduced operation and maintenance costs due to long life time
- Instant and constant light output over the lamp life
- Flicker-free operation
- Mercury-free

Product features

- Dimmable
- Available with connector combinations A, B, C/Z on request
- Infrared radiation output that provides light in the worst of conditions

Technical data

Electrical data



Nominal voltage	9.8 V
Nominal wattage	65 W
Nominal current	6.60 A

Light technical data

Luminous flux	1450 lm
----------------------	---------

Dimensions & weight

Diameter	13.5 mm
Length with base excl. base pins/connection	32.00 mm
Mounting length	16.0 mm
Light center length (LCL)	20.0 mm
Length	48.0 mm

*Product line drawing**Base***Lifespan**

Lifespan	1500 h
-----------------	--------

Additional product data

Base (standard designation)	PK30d
------------------------------------	-------

Capabilities


Burning position	s90
-------------------------	-----

Country specific categorizations

Order reference	64328 HLX
------------------------	-----------

Safety advice

To prevent personal injury or damage to property, halogen lamps may only be operated in suitable luminaires designed with suitable mechanisms (protective shields, grids, etc.) to ensure that in the event of a lamp bursting no parts/shards can escape and that during operation no ultraviolet radiation can escape. There must also be a warning sign to indicate that the lamps give off high levels of heat. Detailed information is available on request.



Burning position

References / Links

For more information on airfield lamps see the brochure:

"The reliable guiding stars - Effective solutions for airfield lighting: Tungsten halogen lamps and LED light sources".

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.