

LED-18W DC 700mA**Standards**


Converter meets CE standard
 Pending UL and C-UL
 VDE and VDE EMV approval

Available Version

901018700-LED 18W DC 700mA
 (Plastic casing)

Mechanical and Thermal

Dimensions (mm) 32 x 45 x 158
 Dimensions (in.) 1.26 x 1.77 x 6.22
 Weight 140 grams, 4.94 ounces
 Tc Max 90°C
 Ta Max 50°C
 PC plastic casing
 Terminal Block Connection

**Electrical**

Load	9-18VA
Input	85-277V 0/50/60Hz
Output current	700mA+/-10%
Output voltage	10-24V
Efficiency	80%
THD max	10%
EMC (RFI)	FCC Class B/EN 55015
Harmonics	EN 61000-3-2
Safety	EN61347-2-2
Immunity	EN 61547/61047
SELV	

Protection and Regulation


Electronic internal resettable short circuit protection.
 Thermal protection and overload regulation.

See reverse side for more information →



LED-18W DC 700mA

Mounting Instructions



Safety Instructions:

1. Always disconnect power before installation and/or removal of the unit.
2. Install in accordance with national and local electrical codes.
3. Wires: Input and output wires 0.75mm² or 18 AWG.