




LAY OUT
P.C.B -HOLE

(FRONT SIDE)



PERFORMANCE CHARACTERISTICS

CURRENT RATING 1.5A AT 20°C (FULLY LOADED)
 1 A AT 70°C (FULLY LOADED)

RATED VOLTAGE : 500 V AC (CONT /CONT)

OPERATING TEMPERATURE : -55°C TO 125°C

CONTACT RESISTANCE 20 MΩ MAX


INSERTION FORCE : 0.75N MAX/CONT

EXTRACTION FORCE : 0.15N MIN/CONT

INSULATION RESISTANCE : $10^4 \text{ M}\Omega \text{ MIN}$

LEAD FREE INDICATOR :LF=LEAD FREE

NOTES



2. THIS PRODUCT IS CSA APPROVED.
THIS PRODUCT IS UL RECOGNIZED.
3. FOR RECOMMENDED PTH DIMENSIONS REFER DRAWING :BS.A.201572.001
4. THIS PRODUCT (LF) MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY
REGULATIONS AS DESCRIBED IN GS-22-008

rev	ecn no	dr	date
A	CONVERSION REVISION 00	KN	14-09-01
B	104-0109	ALEX B	27-11-04
C	DG05-0278	Kason	02-08-05
D	DG10-0110	NZ	2010.9.3
-	-	-	-
-	-	-	-
-	-	-	-

Material			Spec ref						
Mat code			✓ tolerance 1DEC±0.2 1DEC 2DEC±0.1 2DEC ANGLES±1° HOEREN			projection		MM	
Heat treat									
Plating/Finish									
Dr	M.Fret	30-10-97				size	Scale		
Eng			Product family			MILLIPACS	A4	2.000	
Chr			Model Name			ECN			
Appr			Model Revision			REL Level			
		title MILLIPACS 2/TYPE A (W/O LOC.PEG)/SHIELDED				dwg no BSC201907009			Rev D
Pro/E file		catalog no		HM2S10PE5101----		CUSTOMER DRAWING		sheet 1 of 1	