





D

C

B

A



- HOUSING AND LATCHES: PCT, UL94 V-0 RATED, COLOR RED. POSTS: BRASS.
- POSTS: GOLD FLASH OVER PALLADIUM-NICKEL PLATE, 0.76 μ m [.000030] MIN TOTAL ON THE LOCALIZED PLATE AREA, 2.54 μ m [.000100] MIN TIN PLATE ON THE SOLDER-TAIL, 1.27 μ m [.000050] MIN NICKEL UNDERPLATE ON THE ENTIRE POST.
-OR-
0.76 μ m [.000030] MIN GOLD PLATE ON THE LOCALIZED PLATE AREA, 2.54 μ m [.000100] MIN TIN PLATE ON THE SOLDER-TAIL, 1.27 μ m [.000050] MIN NICKEL UNDERPLATE ON THE ENTIRE POST.
- DISTANCE REQUIRED BY LATCHES IN OPEN POSITION.
- RECOMMENDED PRINTED CIRCUIT BOARD THICKNESS 1.57 [.062].
- RECOMMENDED PAD THICKNESS 0.25 [.010].
- DATUMS -M- & -N- TO BE ESTABLISHED BY CUSTOMER.

60.98 [2.400]	68.58 [2.700]	72.64 [2.860]	78.74 [3.100]	82.80 [3.260]	50	1-5111922-0
30.48 [1.200]	38.10 [1.500]	42.16 [1.660]	48.26 [1.900]	53.32 [2.060]	26	5111922-6
48.26 [1.900]	55.88 [2.200]	59.94 [2.360]	66.04 [2.600]	70.10 [2.760]	40	5111922-9
17.78 [.700]	25.40 [1.000]	29.46 [1.160]	35.56 [1.400]	39.62 [1.560]	16	5111922-3
10.16 [.400]	17.78 [.700]	21.84 [.860]	27.94 [1.100]	32.00 [1.260]	10	5111922-1
E	D	C	B	A	NUMBER OF POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2009.		DWN G. ATTADIA - 01-12-05 CHK S. BOLASH - 01-12-05	TE Connectivity	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD M. WALMSLEY - 01-12-05	NAME	
	0 PLC $\pm$ -	PRODUCT SPEC	108-40018	
	1 PLC $\pm$ -	APPLICATION SPEC	-	
	2 PLC $\pm$ 0.13 [.005]			
	3 PLC $\pm$ -			
	4 PLC $\pm$ -			
MATERIAL	FINISH	WEIGHT	SIZE CAGE CODE DRAWING NO	
		-	A1 00779 5111922	
CUSTOMER DRAWING		SCALE 4:1	SHEET 1 OF 1	REV E