



MICRODRIVER MLV3



FEATURES / BENEFITS

- ▲ 10-30 Volt DC input
- ▲ Compact in size
- ▲ Very lightweight
- ▲ Short and open circuit protected
- ▲ 350mA or 700mA models available

OPERATING CONDITIONS

- ▲ Operating Ambient Temperature -10°C to +70°C
- ▲ Maximum case temperature 85°C
- ▲ Input voltage 10-30VDC
- ▲ 350mA version drives 1-3 LEDs, V_{out} : 3-12VDC
- ▲ 700mA version drives 1 to 2 LEDs with min 12V input & 1 to 4 LEDs with min 23V input, V_{out} : 4-18VDC

MECHANICAL DIMENSIONS

51.0mm X 32.0mm X 18.0mm
(2.01" X 1.26" X 0.71")

APPLICATION

- ▲ Low voltage track lighting
- ▲ Landscape lighting
- ▲ Emergency lighting
- ▲ Signage
- ▲ Vehicle lighting
- ▲ Beacons and signage

PART NUMBERS

MLV3-C-35 : 350mA version
MLV3-C-70 : 700mA version

Dialight reserves the right to make changes at any time
in order to supply the best product possible.


Dialight Corporation

1501 Route 34 South • Farmingdale, NJ 07727 USA
Tel: (1) 732-919-3119 • Fax: (1) 732-751-5778 • www.dialight.com




MDEXLUMMLV3_B

MECHANICAL DRAWING



WIRING INFORMATION (350MA VERSION)



Dialight reserves the right to make changes at any time in order to supply the best product possible.

Dialight Corporation

1501 Route 34 South • Farmingdale, NJ 07727 USA

Tel: (1) 732-919-3119 • Fax: (1) 732-751-5778 • www.dialight.com



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Dialight:

[MLV-3C70](#) [MLV-3C35](#)