


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	OWN	APVD
G	14		C	REV PER ECR 06-005021	01MAR06	JR	TM

D



C

B



A

- STAMP AMP 4* APPROX AS SHOWN
- 2 MAX RECOMMENDED OPERATING TEMP IS 170°C MAX
- 3 VOLTAGE RATING, NOT APPLICABLE
- 4 WIRE CROSS SECTION AREA:
16.8-26.7mm² [33,100-52,600] CIR MIL
SOLID OR STRANDED
- 5 COPPER PER ASTM B-152, ANNEALED
- 6 TIN PLATE 0.00254 [.000100] MIN PER ASTM B545

D

C

160075

B

A

100	LOOSE PIECE	160075
QTY	PACKAGING TYPE	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	JR RUTH	01MAR06	tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608								
		CHK	T MICHIELUTTI	01MAR06									
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	T MICHIELUTTI	01MAR06	NAME						
		PRODUCT SPEC		TERMINAL, RING TONGUE, SOLISTRAND —									
		—											
		APPLICATION SPEC											
		—											
MATERIAL		FINISH		WEIGHT		—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO			
				A2		00779	C=160075		—				
CUSTOMER DRAWING								SCALE	4:1	SHEET	1 of 1	REV	C