







THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


| LOC | DIST | REVISIONS   |     |    | DATE         | DWN     | APVD  |
|-----|------|-------------|-----|----|--------------|---------|-------|
| P   | LTR  | DESCRIPTION |     |    |              |         |       |
| J   | —    | P           | LTR | J6 | FJA0-0541-03 | 19SEP03 | TS KB |



- ① TO BE MEASURED WITHIN 2mm FROM [-Z-]  
2. APPLICABLE P.C.BORD THICKNESS: 1.6mm  
3. THE MATING PLUG HOUSING PART NUMBER: 174045  
4. RECOMMENDED MOUNTING SCREW; 3mm DIA, 7mm LENGTH (MIN.)  
PAN HEAD, CLASS 2 TAPPING SCREW SPECIFIED IN JIS B1115,  
B1122 (TIGHTENING TORQUE: 0.4N·m MAX.)


- ⑤ CIRCUIT NUMBER.  
⑥ PRELIMINARY NOT FOR PRODUCTION.

- ① [-Z-] 面より 2mm の範囲で測定。  
2. 適用プリント基板厚: 1.6mm  
3. 嵌合相手型番: 174045  
4. 推奨取付けねじ: JIS B1115, B1122 タッピングねじ、なべ2種  
呼び径3、長さ7mm以上 (締付けトルク: 0.4N·m 以下)  
⑤ 回路番号: 上図参照のこと。  
⑥ 非量産対象製品。



| TOLERANCE UNLESS OTHERWISE SPECIFIED: |       |
|---------------------------------------|-------|
| 一般公差                                  |       |
| 0 < x ≤ 10                            | ±0.2  |
| 10 < x ≤ 30                           | ±0.25 |
| 30 < x ≤ 100                          | ±0.3  |
| ANGLE ;                               | ±3°   |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
単位: 概  
MMMATERIAL  
材料  
HOUSING: PBT  
CONTACT: BRASSTOLERANCES UNLESS OTHERWISE SPECIFIED:  
一般公差  
0 PLC ±  
1 PLC ±  
2 PLC ±  
3 PLC ±  
4 PLC ±  
ANGLES ±

SEE TABLE

|                  |              |          |
|------------------|--------------|----------|
| DWN              | T. SHINOHARA | 19OCT00  |
| CHK              | A. YAMAGUCHI | 19OCT00  |
| APVD             | K. BETSUI    | 19OCT00  |
| PRODUCT SPEC     | 製品規格         | 108-5244 |
| APPLICATION SPEC | 取付適用規格       |          |
| WEIGHT           | 7g           |          |
| CUSTOMER DRAWING |              |          |

|                                                                                                               |           |                                              |               |
|---------------------------------------------------------------------------------------------------------------|-----------|----------------------------------------------|---------------|
| WIRE RANGE<br>包合電線斷面積                                                                                         |           | INSULATION DIA<br>被覆外徑                       |               |
| <b>tyco</b><br><b>Electronics</b>                                                                             |           | Tyco Electronics AMP K.K.<br>Kawasaki, Japan |               |
| NAME<br>名稱<br><br>040 SERIES MULTI-LOCK I/O CONNECTOR<br>12POSITION CAP HOUSING ASSEMBLY<br>(HORIZONTAL TYPE) |           |                                              |               |
| SIZE                                                                                                          | CAGE CODE | DRAWING NO<br>番 号                            | RESTRICTED TO |
| A3                                                                                                            | 00779     | C-174051                                     | —             |
| SCALE<br>尺 度                                                                                                  |           | SHEET                                        | REV           |
| 2-1                                                                                                           |           | 1 OF 1                                       | J6            |