




DUAL-IN-LINE SOCKETS

SERIES 115...003 • ULTRA LOW PROFILE • OPEN FRAME



- Our lowest profile DIP socket with an above PCB height of only .095"
- Special short Hi-Rel, 4-finger BeCu #12 contact is rated at 3 amps. See page 252 for details
- Series 115 uses MM #1534 pins. See page 161 for details
- Insulators are high temperature thermoplastic, suitable for all soldering operations
- For Electrical, Mechanical and Environmental Data, see page 264 for details



Total number of pins				Quantity per tube	ORDERING INFORMATION							
	A	B	C									
6	0.3	0.3	0.4	68	115-XX-306-41-003000							
8	0.4	0.3	0.4	50								
14	0.7	0.3	0.4	28	115-XX-314-41-003000							
16	0.8	0.3	0.4	25								
18	0.9	0.3	0.4	22	115-XX-318-41-003000							
20	1.0	0.3	0.4	20								
22	1.1	0.3	0.4	18	115-XX-322-41-003000							
24	1.2	0.3	0.4	16								
28	1.4	0.3	0.4	14	115-XX-328-41-003000							
20	1.0	0.4	0.5	20								
22	1.1	0.4	0.5	18	115-XX-422-41-003000							
24	1.2	0.4	0.5	16								
28	1.4	0.4	0.5	14	115-XX-428-41-003000							
24	1.2	0.6	0.7	16								
28	1.4	0.6	0.7	14	115-XX-628-41-003000							
32	1.6	0.6	0.7	12								
36	1.8	0.6	0.7	11	115-XX-636-41-003000							
40	2.0	0.6	0.7	10								
48	2.4	0.6	0.7	8	115-XX-648-41-003000							
50	2.5	0.6	0.7	8								
					XX=Plating Code See Below							
					RoHS-2 2011/65/EU							
SPECIFY PLATING CODE XX =						91	93		41	43	44	
Sleeve (Pin) 						200 μ" Sn/Pb	200 μ" Sn/Pb		200 μ" Sn	200 μ" Sn	200 μ" Sn	
Contact (Clip) 						10 μ" Au	30 μ" Au		10 μ" Au	30 μ" Au	100 μ" Sn	