


Terminal Block Plugs

158-P02EC381RP Series



Terminal Block Plugs



Dimensions: mm (In.)

P	02P	03P	04P	05P	06P	07P	08P	09P	10P	11P	12P
U mm	3.81	7.52	11.43	15.24	19.05	22.86	28.67	30.48	34.29	38.10	41.91
V mm	8.41	12.22	16.03	19.84	23.85	27.48	31.27	35.08	38.89	42.70	48.51

ELECTRICAL SPECIFICATIONS

Rating:	300V 8A
Pitch:	3.81 mm
Insulation withstands voltage:	AC 1000V/Min
Insulation resistance:	1000MΩ or more at DC500V
Temperature range:	-40°C~ +120°C
Electric wire:	22 ~ 16 AWG

MATERIAL SPECIFICATIONS

Base Housing:	PBT, Green
Clamp:	Bronze
Wire Cage:	Steel, Ni Plated
Screw:	Steel, M2/Zn Plated
Top Housing:	PBT, Green

Date Last Revised: 6-27-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC- 300768

158-P02EC381RP Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Kobiconn:

[158-P02EC381RP](#) [158-P04EC381RP](#) [158-P06EC381RP](#)