

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

- . - .




COPYRIGHT


BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC —	DIST —	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	REDRAWN W/CHANGE FJ00-1446-00	05SEP00	TS	KB





-1;本図
-1;AS SHOWN




1. 嵌合相手端子型番 : 171632

1. THE MATING RECEPTACLE PART NUMBER : 171632



WIRE RANGE 抱合電線断面積		1.25~3mm ²		INSULATION DIA 被覆外径		2.5~4.1mm	
D		AMP Tyco Electronics AMP K.K. Kawasaki, Japan					
D							
D							
NAME 名称		250 SERIES TAB CONTACT FOR SEALED CONNECTOR —					
SIZE		CAGE CODE		DRAWING NO 番号		RESTRICTED TO	
A3		00779		C-171633		—	
SCALE 尺度				5:1		SHEET	
						1 OF 1	
						REV	
						A	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位: 括
MMMATERIAL
材料
BRASS t=0.4TOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±FINISH
仕上

TOLERANCE UNLESS
OTHERWISE SPECIFIED:
一般公差

0 < x ≤ 10 : ±0.2
10 < x ≤ 30 : ±0.25
30 < x ≤ 100 : ±0.3

ANGLE ; ±3°
角度