








CLOSED FOR
MOLDING PURPOSES

SECTION A-A
SCALE 10:1

SECTION B-B
SCALE 10:1

METRIC

F or 0	3.56 [.140]	5.33 [.210]	F	2.29 [.090]	1.68 [.065]	1.3mm ² [.16]
					1.50 [.059]	0.8mm ² [.18]
					1.42 [.056]	0.5mm ² [.20]
TYPE	WIDTH	STRIP LENGTH ±0.38 [±.015]	TYPE	WIDTH	±0.051 [.002]	WIRE
INSUL BARREL			WIRE BARREL	CRIMP		

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm TOLERANCES ON: 2 PLC DEC ± 0.25 [.010] 3 PLC DEC ± 0.25 [.010] ANGLES ±	DR 7/26/90 P FORNEY	CHK 7/26/90 JR RUTH	APPD 7/26/90 G VETTER	APPD 7/26/90 R KUO	PRODUCT SPEC	FINISH 0.003302 [.000130] MAX PRE-TIN PL PER MIL-T-10727
#1 HARD BRASS	2.41-2.92 DIA [.095-.115]	0.5mm ² -1.3mm ² [20-16] AWG	61388-1	WIRE RANGE	PART NO	SCALE 6:1
INSULATION RANGE	SECTION A-A SCALE 10:1	SECTION B-B SCALE 10:1	AMP Incorporated Harrisburg, PA 17105-3608	NAME SHUR PLUG, 3.96 [.156] DIA	SIZE B	CAGE CODE 00779
APPLICATION SPEC	WEIGHT	SCALE	DRAWING NO 61388	SHEET 1 OF 1		

CUSTOMER DRAWING