



SPECIFICATION :
CURRENT RATING : 1 AMP.
INSULATOR RESISTANCE : 1000 M Ω MIN. (AT 500 V DC)
DIELECTRIC WITHSTANDING VOLTAGE : AC 500 V MIN. (FOR 1 MINUTE)
OPERATING TEMPERATURE : -55°C TO 105°C
CONTACT RESISTANCE : 15m Ω MAX.
INSULATOR MATERIAL : PBT WITH GLASS-FIBER REINFORCED UL 94V-0
CONTACT MATERIAL : BRASS
CONTACT PLATING : GOLD OVER NICKEL
WIRE SIZE : AWG 26 & 28 STRANDED , 1.27mm CONDUCTOR CENTRE FLAT CABLE



37	63.50/(2.50)	69.40/(2.732)	49.86/(1.963)	47.09/(1.854)	54.60/(2.150)	57.10/(2.2)
25	47.04/(1.852)	53.09/(2.090)	33.24/(1.309)	30.47/(1.200)	38.14/(1.502)	40.50/(1.61)
15	33.32/(1.312)	39.10/(1.539)	19.39/(.763)	16.62/(.654)	24.00/(.945)	26.60/(1.04)
9	24.99/(.984)	30.86/(1.212)	11.08/(.436)	8.31/(.327)	16.10/(.634)	18.60/(.73)
NO. OF POSITIONS	A ±0.13 A (±0.05)	B ±0.25 B (±0.10)	C ±0.13 C (±0.05)	D ±0.13 D (±0.05)	E ±0.25 E (±0.10)	F ±0.25 F (±0.10)

55.45/(2.183)	59.08/(2.326)	60.73/(2.391)
38.96/(1.534)	42.52/(1.674)	44.27/(1.743)
23.25/(.994)	28.80/(1.134)	30.53/(1.202)
16.92/(.666)	20.47/(.806)	22.20/(.874)
± 0.25 (± 0.10)	± 0.13 (.005) REAR MOUNTS	± 0.13 (.005) FRONT MOUNTS

ORDER INFORMATION

C0580 —

XX

CONTACT NO.
09 , 15 , 25 , 37

CONTACT TYPE:
M
M : Male

RODY	OPTION
	X

A : Metal Shell W/D S/R
B : Metal Shell W/Metal S/R
C : Metal Shell W/Plastic S/R
D : Plastic Shell W/D S/R
E : Plastic Shell W/Metal S/R
F : Plastic Shell W/Plastic S/R

MOUNTING
OPTION:
☒ X

A : Through Hole
B : Thread Insert
4-40 UNC
C : Thread Insert M3

CONTACT
PLATING:
☒ X

S : Selective Gold
G : Gold Flash
A : Gold 50µ
B : Gold 100µ
C : Gold 150µ
D : Gold 300µ

INSULATOR
COLOR

X

B : Black
G : Grey
L : Blue

0

R

RoHS Compliant

玄茂科技股份有限公司
HSUAN MAO TECHNOLOGY CO., LTD.

UNIT

SCALE

PART NAME

制表日: 2006/02/13

DRAWING

APPROVED

APPD.

CKD

TOLERANCE

PART NO.

REV.