



- Square caps
- Different top surfaces: flat, convex or concave
- 14.3 mm x 14.3 mm
- h = 19.1 mm; 20.2 mm; 20.1 mm
- Material: ABS/polycarbonate
- Temp. Range:
 - Solid cap: -40/+65°C
 - Transparent cap: -40/+85°C
- Panel cut-out: 1KS/1KBS/1KCS-14.7 x 14.7




Custom solution

DIMENSIONS


SMD w/LED + 1KS




TH w/LED + 1KBS



SMD w/LED + 1KCS



Bezel (optional)



ILLUMINATED – HOW TO ORDER

Switch	Mounting	Actuation force	LED	Cap	Bezel
5 G				+ 1 1 1 6 +	2 K
	TH9 through-hole	20	01 blue	Frosted white lens and transparent lid	03 grey
	SH9 surface mount	35	22 green		06 white
		65	42 yellow		08 red
		Q*	61 white	1KS 	09 black
			82 red	1KBS 	
			2242 green/yellow		
			8222 red/green		
			8242 red/yellow		

*For an illuminated quiet 2.0N switch add Q

*For an illuminated quiet 2.0N switch add Q to the end of the switch part number.

NON-ILLUMINATED- HOW TO ORDER

<u>Switch</u>	<u>Mounting</u>	<u>Actuation force</u>	<u>Cap</u>	<u>Bezel</u>
5 G			1 K S 1 6	2 K
TH9 through-hole	20	Frosted white lens		03 grey
SH9 surface mount	20Q	1KS		06 white
	35			08 red
	65			09 black
			Colour code	
			00 blue	
			02 green	
			03 grey	
			04 yellow	
			06 white	
			08 red	
			09 black	

Ordering example:

5GTH93501+1KCS1116+2K09 with illumination OR 5GSH965+1KS09+2K03 without illumination OR *5GTH92082Q (illuminated quiet version)

Please see colour codes, updates of products and changes of specifications on www.mec.dk