



SLEEVE

DIMPLED SURFACE



- 1 STAMP AMP 8* LOCATE APPROX AS SHOWN
2. TONGUE MATERIAL THK 1.02±0.08 [.040±.003]
3. WIRE INSULATION DIA 9.14 [.360] MAX

AMP WIRE RANGE	FILE E13288	LR7189 Certified
8 AWG STRANDED	8 AWG STRANDED	8 AWG STRANDED

100	LOOSE PC	55654-1
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS

MAX RECOMMENDED OPERATING
TEMPERATURE:

90°C

VOLTAGE RATING:
600 V MAX

CIRCULAR MIL AREA:
6.64-10.54mm² [13,100-20,800]
STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN mm [INCHES]
TOLERANCES ON:
2 PLC DEC ± 0.20 [.008]
3 PLC DEC ± -
ANGLES ± -

MATERIAL
COPPER PER ASTM B-152
PVC, COLOR:RED

FINISH
TIN PLATE
PER MIL-T-10727

DR 10-12-93
S.S. GOULDEN

CHK 10-12-93
R. HERSEY

APPD 10-12-93
B. BARE

APPD 10-12-93
M.ELLIS

PRODUCT SPEC
NOT AVAILABLE

APPLICATION SPEC
NOT AVAILABLE

WEIGHT -

AMP

AMP Incorporated
Harrisburg, PA 17105-3608

NAME
TERMINAL, RING TONGUE-BENT 90°,
PLASTI-GRIP, WIRE SIZE:8 AWG

SIZE
B

CAGE CODE
00779

DRAWING NO
C-55654

SCALE
NTS

SHEET
1 OF 1