



FGxx

METAL FAN GUARDS



FG25



FGxxx

Finger Guards for standardized fan sizes 25x25mm up to 172x150mm. Material: steel wire chromium plated.

Art. No.	Type	Fan Size [mm]	D [mm]	No. Of Rings	Height [mm]	Packing [PCs]
912510000	FG25 Fan Guard	25x25	1x28.2	2	5	100
913010000	FG30 Fan Guard	30x30	4x24	2	5	100
914010000	FG40 Fan Guard	40x40	4x32	2	5	100
915010000	FG50 Fan Guard	50x50	4x42	3	5	100
915010001	FG50-40 Fan Guard	50x50	4x40	3	5	100
916010000	FG60 Fan Guard	60x60	4x50	4	5	100
918010000	FG80 Fan Guard	80x80	4x71.5	5	5	100
919210000	FG92 Fan Guard	92x92	4x82.5	6	5	100
911210000	FG120 Fan Guard	120x120	4x105	8	5.7	100
912710000	FG127 Fan Guard	127x127	4x113.3	8	6.0	100
915110000	FG150 Fan Guard	172/150	1x162	9/10	6.5	100
917210000	FG172 Fan Guard	Ø150, 172x150	1x162	10	6.5	100



Plastic fan guards (IP 20) for standard fans
 Sizes 40x40 mm up to 120x120 mm and Ø150

914020000	FG40K Plastic Fan Guard, IP20	40x40	42.3x42.3x3.3	100
916020000	FG60K Plastic Fan Guard, IP20	60x60	60x60x6.0	100
918020000	FG80K Plastic Fan Guard, IP20	80x80	81x81x5.5	100
919220000	FG92K Plastic Fan Guard, IP20	92x92	92x92x5.5	100
911220000	FG120K Plastic Fan Guard, IP20	120x120	121x121x6.5	100
911520000	FG150K Plastic Fan Guard, IP20	Ø150, 150x172	173x173x10.8	50

