

BACKSHELLS FOR METAL SHELL "D" CONNECTORS 50 POSITIONS



PHYSICAL PROPERTIES

INSULATION MATERIAL: Glass filled thermoplastic,
rated UL 94V-0

COLOR: Black.

INSULATION MATERIAL (SHIELDED): glass filled
thermoplastic, rated 94V-0, chrome electroplated

ELECTRICAL PROPERTIES

SHIELDING EFFICIENCY: >40dB @ 100 MHz to 1 GHz




ENVIRONMENTAL PROPERTIES

TEMPERATURE RATING: -55°C to 125°C

APPLICATION TOOLING

HAND TOOL	779-2100
with Die (Flat Cable Outlet)	779-2173
with Die (Round Cable Outlet)	779-2174
BENCH PRESS (MANUAL)	779-3200
BENCH PRESS (PNEUMATIC)	779-3500XT
with Platen and Base Plate (Flat Cable Outlet)	779-3173
with Platen and Base Plate (Round Cable Outlet)	779-3174

① Use for Bail Lock Assembly 609-50BL



Ordering Information

CATALOG NUMBERS BACKSHELL WITH CABLE OUTLET				FOR CONNECTOR TYPES SERIES 622	NO. OF POS.	ROUND CABLE			
FLAT CABLE	ROUND CABLE	FLAT CABLE (METALLIZED)	ROUND CABLE (METALLIZED)			JACKET Ø MIN.	JACKET Ø MAX.	DIELECTRIC OR SHIELD Ø MIN.	DIELECTRIC OR SHIELD Ø MAX.
622-050D	622-050DR	622-050DM	622-050DRM	622-50P, M1, M2	50	9.4 (.37)	11.2 (.44)	7.6 (.30)	9.4 (.37)
622-050DI	622-050DRI	622-050DMI	622-050DRIM	622-50P, M1, M2	50*	9.4 (.37)	11.2 (.44)	7.6 (.30)	9.4 (.37)