



Search Results

- Evaluate
- FAQ's
- How to Buy
- Bill of Material
 - Favorite Products List
 - Locate Distributor
- Install & Maintain
- Operation Manuals
 - PDFCT-2002 Hydr ..

Home > Products Overview > Search Results >

Current refinements (click to remove) Search Tips Within Results

Die Type, Battery Powered Hydraulic, 6 Ton, Crimping Tool with Open "C -Head" > Text Search: 'CT-2002'

CT-2002



CT-2002, Carrying Case, Two NiCd Rechargeable Batteries with LED display, One Battery Charger and One Shoulder Strap.

- Battery powered, provides fingertip operation
- Self-contained unit, completely portable
- Lightweight and ergonomically balanced for easy operation without fatigue
- Develops 6 tons of crimping force, crimps copper compression lugs and splices up to 500 kcmil
- Provides UL Listed and CSA Certified connections on *PANDUIT® Pan-Lug™* Copper Lugs, Splices, and Taps
- Open "C-Head" design allows easy loading of crimping dies and connectors, saves time
- Rubber boot on crimp head provides abrasion

Related Products

- CD-2001 Crimping Dies
- CDM2001 Crimping Dies
- Accessories for Battery Powere ..

protection

- Audible "pop-off" valve indicates crimp completion
- Tool provided with two, NiCd rechargeable batteries and battery charger to allow for continuous operation
- High productivity, up to 80 crimps on 500 kcmil copper lugs and splices on a single battery charge
- Six to eight second crimp cycle time provides quick terminations, saves time
- Battery charger charges expended batteries completely in 25 minutes
- Batteries include LED battery charge indicators for visual indication of current battery charge
- Battery charger includes battery reconditioner feature which prevents battery memory build -up and provides over 1,000 battery recharge cycles resulting in long life
- Uses color -coded crimping dies to provide easy matching of crimping die to connector
- Embosses die index number on connector barrels to provide post crimp inspection
- Dies installed using spring loaded die retention pins, no need for tools
- Crimp head rotates 180 degrees to provide versatility for use in restricted spaces

■ Part Number	CT-2002
■ RoHS Compliancy Status	RoHS directive is not applicable
■ Part Description	Terminates <i>PANDUIT® Pan-Lug™</i> Compression Connectors: • Copper compression lugs and splices for #8 AWG – 500 kcmil code conductor • Copper compression lugs for #8 AWG – 350 kcmil flex conductor • Copper compression CTAPF taps for #10– 3/0 AWG code conductor • Copper compression CTAP taps for #8– #2 AWG code conductor • <i>PANDUIT® Pan-Term®</i> Tubular Terminals for #8 AWG– 250 kcmil code conductor Specifications: Output: 6 tons Jaw opening: .95" Weight: 9.0 lbs. with battery Length: 13" Height: 12" Width: 3" Warranty: 5 years tool, 1 year on batteries CT-2002 includes: • Tool • Two CT-BC25, 14.4 VDC rechargeable batteries with LED display • One CT-CHR25 battery charger • One shoulder strap • Plastic tool case with storage for batteries, shoulder strap, and crimping dies • Tool incorporates D3 die pocket (included with tool)
■ Product Type	Tools - Hydraulic
■ Pricing Description	Battery Powered Hydraulic Crimping Tool, Die Type, 6 Ton, with Open "C" Head
■ Min. Order UOM	PC
■ Min. Order Qty.	1
■ BOM Qty. (# of Pkgs.)	0
■ Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.