



General Information

Kit Part Number:	2110838-8
Description:	Uninsulated Spade Tongue Terminal Kit
Application:	Appliance Industries, Heavy Equipment, Instrumentation and Controls, Motors, Pad and Pole Mount Transformers, Panel Boxes, Power Supplies, Switchgear, Telecommunications, Transportation
Family:	SOLISTRAND
TE Brand:	AMP Products
Solution:	MRO (Maintenance, Repair and Operation)
Product Type:	Terminals & Splices
Number of Pieces:	120
RoHS:	Yes

Specifications

Body and Plating:	Tin Plated, Copper Body
Insulation:	Non-Insulated
Stud/Tab Size:	2, 4, 6, 8, 10
Temperature Rating:	170 Degrees C (Max)
Terminal Type:	Spade Tongue
Tool Included:	No
Wire Gauge (AWG):	12-10, 16-14 , 22-16

Product Highlights

SOLISTRAND terminals and splices are especially designed to terminate solid and stranded wire, irregular shaped conductors, and combinations of these, while still retaining the superior performance characteristics of single purpose terminals and splices. Because TE Connectivity matches the terminal to the tool, each termination is uniformly perfect making quality control easy and performance consistent. Corrosion resistance, vibration resistance and tensile strength of these terminals and splices are well within the limits of commercial and military specifications. The SOLISTRAND line includes terminals, parallel and butt splices, flat rings, spades, hooks, and flanged tongue terminals in sizes from 26 AWG [0.1mm²] through 600 MCM [304mm²].

Features and Benefits

- Brazed seam for uniform metal strength around the entire barrel area
- Brazed seam also prevents pinched wires
- "W" crimp provides excellent electrical performance and higher tensile strength
- Dimples or serrations inside the wire barrel provide optimum tensile strength and maximum electrical contact area after crimping
- Bell mouth on barrel entrance makes insertion of wires easier
- Product is rated for 170 degrees C maximum

Applications

- Pad and Pole Mount Transformers
- Power Supplies
- Motors
- Switchgear
- Telecommunications
- Appliances
- Panel Boxes
- Heavy Equipment

- Instruments / Control
- Transportation





Bill of Materials

Part No.	Qty In Kit	Description	Datasheet	P/N Details	Search Distributors Inventory
53555-1	10	Spade Tongue Terminal, 22-16 AWG with Stud Size 2	Datasheet	Details	Search
321463	10	Spade Tongue Terminal, 22-16 AWG with Stud Size 4	Datasheet	Details	Search
36195	10	Spade Tongue Terminal, 22-16 AWG with Stud Size 6	Datasheet	Details	Search
34117	10	Spade Tongue Terminal, 22-16 AWG with Stud Size 8	Datasheet	Details	Search
34583	10	Spade Tongue Terminal, 22-16 AWG with Stud Size 10	Datasheet	Details	Search
322996	10	Spade Tongue Terminal, 16-14 AWG with Stud Size 6	Datasheet	Details	Search
34128	10	Spade Tongue Terminal, 16-14 AWG with Stud Size 8	Datasheet	Details	Search
34129	10	Spade Tongue Terminal, 16-14 AWG with Stud Size 10	Datasheet	Details	Search
322451	10	Spade Tongue Terminal, 12-10 AWG with Stud Size 6	Datasheet	Details	Search
32995	10	Spade Tongue Terminal, 12-10 AWG with Stud Size 8	Datasheet	Details	Search
33479	10	Spade Tongue Terminal, 12-10 AWG with Stud Size 10	Datasheet	Details	Search
35495	10	Spade Tongue Terminal, 12-10 AWG with Stud Size 10	Datasheet	Details	Search

Recommended Tool

Part No.	Included in Kit
58546-1	No





