


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

| PANDUIT<br>PART NUMBER | STUD<br>SIZE | DIMENSIONS in. |               |               |                |               |
|------------------------|--------------|----------------|---------------|---------------|----------------|---------------|
|                        |              | A $\pm .03$    | W $\pm .01$   | C $\pm .02$   | M $\pm .03$    | H $\pm .01$   |
| PV14-6LF               | #6           | .90<br>(22.86) | .25<br>(6.35) | .22<br>(5.59) | .68<br>(17.27) | .14<br>(3.56) |
| PV14-6LFW              | #6           | .90<br>(22.86) | .29<br>(7.37) | .22<br>(5.59) | .68<br>(17.27) | .14<br>(3.56) |
| PV14-8LF               | #8           | .97<br>(24.64) | .29<br>(7.37) | .25<br>(6.35) | .73<br>(18.54) | .16<br>(4.06) |
| PV14-10LF              | #10          | .97<br>(24.64) | .33<br>(8.38) | .25<br>(6.35) | .73<br>(18.54) | .19<br>(4.83) |
| PV14-10LFN             | #10          | .97<br>(24.64) | .29<br>(7.37) | .25<br>(6.35) | .73<br>(18.54) | .19<br>(4.83) |

NOTES:

- UL LISTED & CSA CERTIFIED FOR
  - 600 V. MAX. VOLTAGE RATING (1000 V. MAX. IN SIGNS, FIXTURES AND LUMINAIRES.)
  - 18-14 AWG SOLID OR STRANDED COPPER WIRE & 221°F (105°C) MAX TEMP RATING, WITH THE CT-500 & CT-550, CT-1550, CT-1551 INSTALLATION TOOLS.
  - 16-14 AWG SOLID OR STRANDED COPPER WIRE & 167°F (75°C) MAX TEMP RATING WITH THE CT-100 INSTALLATION TOOLS.
- MATERIAL:
  - STAMPING - .032 (.81) THK COPPER, TIN PLATED
  - HOUSING - VINYL, BLUE
- STRIP LENGTH 5/16  $\pm 1/32$  -0
- PACKAGE QTY.: -C=100/-M=1000
- DIMENSIONS IN BRACKETS ARE IN MILLIMETERS



LISTED  
587H  
E52164



CERTIFIED  
LR31212

A41296\_09

|     |      |     |     |                              |       |      |      |                                                                                                      |              |               |                       |
|-----|------|-----|-----|------------------------------|-------|------|------|------------------------------------------------------------------------------------------------------|--------------|---------------|-----------------------|
| 09  | 1-01 |     | RM  | FILESPEC WAS N41296AA_PCD_08 |       |      |      | <div><div>PANDUIT</div><div>CORP.</div><div>TINLEY PARK, ILLINOIS</div></div>                        |              |               |                       |
| 08  |      | JKD |     | ADDED CT-1550 & CT-1551      | 07634 |      |      |                                                                                                      |              |               |                       |
| 7   | 1-95 | MC  | RLS | UPDATED NOTES AND DIMENSIONS | 02896 | LCA  | TFKE | #16-14 BARREL FUNNELED VINYL INSULATED<br>LOCKING FORK, .175 (4.45) MAX. WIRE<br>INSULATION DIAMETER |              |               |                       |
| 6   | 8-88 | DW  |     | REDRAWN WITH REVISIONS       |       |      | JRB  |                                                                                                      |              |               |                       |
| REV | DATE | BY  | CHK | DESCRIPTION                  | ECN # | CUST | PM   | DRAWN BY<br>DAW                                                                                      | CHK'D<br>CJH | SCALE<br>NONE | DRAWING NO.<br>A41296 |