






ITEM	DESCRIPTION
1	SCREW
2	COVER ASSEMBLY
3	INSERT ASSEMBLY
4	GASKET

C81311N62**

SERIES C81- INTERNAL THREAD FORM A
POLES 2= 2 POLE, 3= 3 POLE
THREAD SIZE 09= PG9 11=PG11, 12= 1/2" GAS, M6=M16x1.5, M0=M1201.5
MATERIAL AND HOUSING COLOUR G= PA6 GRAY, N= PA6 BLACK, W= PA6 BLACK V0, T= TRANSPARENT
EARTH POSITION 0= UNMOUNTED, 2= H12, 3= H3, 6= H6, 9= H9
SCREW AND GASKET 1= NBR PROFILE GASKET & SCREW
2= NBR FLAT GASKET & SCREW
3= WHITE SILICON PROFILE GASKET & SCREW
4= WHITE SILICON FLAT GASKET & SCREW
R= INTEGRATED GASKET & SCREW WITH GROMMET, NOT ASSEMBLED

NON STANDARD COMPONENTS
14= SINGLE PACKED IN NEUTRAL BAG

NOTES

- PLEASE SEE SHEET 2 FOR CURRENTLY CONFIGURED PART NUMBERS.
FOR SPECIFIC PART NUMBERS PLEASE CONTACT SALES OR CONSULT
THE INTELLIGENT PART NUMBERS IN THE TABLE ATTACHED.
- EARTH POSITION SHOWN, H6.
- FOR PACKAGING SEE PACKAGING SPEC PK-121023-C81
- PRODUCT SPEC: SEE PS-121201-001
- P/N 1210230637 SHOWN FOR ILLUSTRATION PURPOSES ONLY

LAST INSPECTION NUMBER 2

ADDED PART NUMBER EC NO: IPG2013-0398 2012/09/17 DRWN:JSHEA CHKD:SMGREVY APPR:STGRIFIN 2012/10/15	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 1.5:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			
			mm	INCH	DRAWN BY DSHEA	DATE 2011/05/23	TITLE INTERNAL THREAD C81 SERIES					
			4 PLACES	± ---	± ---	CHECKED BY DMAHER	DATE 2011/05/30	MOLEX MOLEX INCORPORATED				
			3 PLACES	± ---	± ---	APPROVED BY EFOLAN	DATE 2011/06/14	DOCUMENT NO. SD-121023-008				
			2 PLACES	± 0.10	± ---	MATERIAL NO.		SHEET NO. 1 OF 2				
	REV		1 PLACE ± 0.20 ± ---		ANGULAR ± 2 °		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE SHEET 2		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	

