



*Quality Products. Service Excellence.*

## Economy Server Cabinet *DC200 Series*



**Note:** This product line has been discontinued as a stocked series. Information is for reference only. It has been replaced with **RB-DC Series**. For alternative solution assistance, **contact Hammond here** or call: USA (716) 630-7030, Canada and International (519) 822-2960.



### Features:

- Constructed in 16-gauge steel.
- Two pairs of 19" EIA compliant square hole punched rails with rack unit markings.
  - Starter pack of M5 screws and cage nuts included.
  - For 10-32 hardware see the **CAGKIT Series**.
- Locking front door has attractive 4 point latch, curved and ribbed surface for added stability, and can be easily removed and hinged in either direction.
- Rear of cabinet features split locking doors making access easier in tight spaces.
- Pair of removable solid side panels include stiffeners for added strength.

### Specifications:

- Includes two (2) 4" diameter cable entry holes (top) and one (1) 8" x 12" opening (bottom)
- Open frame bottom allows raised tile floor cable and air access.
- Bottom of cabinet includes:
  - Four (4) adjustable leveling feet
  - Four (4) recessed casters
- Rails can adjust in depth in 25mm increments.
- Grounding studs provided on frame.
- Finished in smooth black powder paint.
- Tested to nearly double the suggested load rating of 950 lbs..
- RoHS Compliant.

**RACK BASICS®**

A HAMMOND BRAND



Part of the Rack Basics® line of economy rack solutions.

| Part No.  | Overall Dimensions |       |       | Rack Units | Usable Mounting Dimensions |       |       | Shipping Weight |
|-----------|--------------------|-------|-------|------------|----------------------------|-------|-------|-----------------|
|           | Height             | Width | Depth |            | Height                     | Width | Depth |                 |
| DC2004224 | 47.10              | 23.60 | 43.40 | 24U        | 42.00                      | 19.00 | 38.00 | 280 lb          |
| DC2004242 | 78.60              | 23.60 | 43.30 | 42U        | 73.50                      | 19.00 | 38.00 | 385 lb          |

*Data subject to change without notice*

