






THIS INFORMATION IS CONFIDENTIAL AND IS DISCLOSED TO YOU ON CONDITION THAT NO FURTHER DISCLOSURE IS MADE BY YOU TO OTHER THAN AMP PERSONNEL WITHOUT WRITTEN AUTHORIZATION FROM AMP (TAIWAN) LTD. DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT.

PRINT DIST
DW

METRIC



NUMBER
C-1734493






- NOTE:
- MATERIAL:
HOUSING: NYLON66 UL94V-0, NATURAL COLOR.
CONTACT: BRASS, THICKNESS=0.20MM.
 - FINISH:
CONTACT: 100u" MIN. BRIGHT TIN PLATED ON CONTACT AREA, 30u" MIN. NICKEL UNDERPLATED OVER ALL.
 - NO PIN AT THIS POSITION.
 - WAVE SOLDER CAPABLE TO 240°C PER TYCO TEST SPEC. 109-201, CONDITION A.




E	ADD P/N 9-1470106-6	ECR-07-015293	OH SH	29JUN 2007
LTR	REVISION RECORD	ECN	DWN CHK	DATE

TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.30 2 PLC ±0.20 3 PLC ±0.10 ANGLES ±3°	DWN O. HU 27-JUN-2007	Tyco Electronics Corporation Taipei, Taiwan			
	CHK S. HOU 27-JUN-2007				
MATERIAL SEE NOTE	APVD W.J. KE 27-JUN-2007	NAME 2.0MM PITCH HEADER, DIP, VERTICAL TYPE			
	PRODUCT SPEC 108-57217				
FINISH SEE NOTE	QUALIFICATION TEST REPORT 501-57218	LOC DW	SIZE A ₃	DRAWING NO C-1470109	REV E
	WEIGHT	SCALE --		SHEET 1 OF 2	





3.00	PIN 3 & 4	6.74	8.0	4.0	6	9-1470109-6
2.40		30.74	32.0	28.0	30	8-1470109-0
2.40	PIN 32	32.74	34.0	30.0	32	7-1470109-2
	PIN 30	30.74	32.0	28.0	30	7-1470109-0
	PIN 28	28.74	30.0	26.0	28	6-1470109-8
	PIN 26	26.74	28.0	24.0	26	6-1470109-6
	PIN 24	24.74	26.0	22.0	24	6-1470109-4
	PIN 22	22.74	24.0	20.0	22	6-1470109-2
	PIN 20	20.74	22.0	18.0	20	6-1470109-0
	PIN 18	18.74	20.0	16.0	18	5-1470109-8
	PIN 16	16.74	18.0	14.0	16	5-1470109-6
	PIN 14	14.74	16.0	12.0	14	5-1470109-4
	PIN 12	12.74	14.0	10.0	12	5-1470109-2
	PIN 10	10.74	12.0	8.0	10	5-1470109-0
3.00	PIN 8	8.74	10.0	6.0	8	4-1470109-8
	PIN 6	6.74	8.0	4.0	6	4-1470109-6
		32.74	34.0	30.0	32	3-1470109-2
		30.74	32.0	28.0	30	3-1470109-0
		28.74	30.0	26.0	28	2-1470109-8
		26.74	28.0	24.0	26	2-1470109-6
		24.74	26.0	22.0	24	2-1470109-4
		22.74	24.0	20.0	22	2-1470109-2
		20.74	22.0	18.0	20	2-1470109-0
		18.74	20.0	16.0	18	1-1470109-8
		16.74	18.0	14.0	16	1-1470109-6
		14.74	16.0	12.0	14	1-1470109-4
DIM D		12.74	14.0	10.0	12	1-1470109-2
		10.74	12.0	8.0	10	1-1470109-0
		8.74	10.0	6.0	8	1470109-8
		6.74	8.0	4.0	6	1470109-6
	3 OMITTED PIN	DIM C	DIM B	DIM A	POS.	PART NUMBER





POLY BAG
127mm(L)X 203mm(W)X 0.07mm(H)




INEER BOX
320mm(L)X 220mm(W)X 155mm(H)



INEER BOX
320mm(L)X 220mm(W)X 155mm(H)



CARTON
340mm(L)X 470mm(W)X 365mm(H)
(FOR HEADER 12P~32P ONLY)



CARTON
340mm(L)X 470mm(W)X 178mm(H)
(FOR HEADER 6P~10P ONLY)

23,400	650		9-1470109-6
10,240	160		8-1470109-0
10,240	160	7-1470109-2	3-1470109-2
10,240	160	7-1470109-0	3-1470109-0
10,240	160	6-1470109-8	2-1470109-8
14,400	200	6-1470109-6	2-1470109-6
14,400	200	6-1470109-4	2-1470109-4
14,400	200	6-1470109-2	2-1470109-2
16,000	250	6-1470109-0	2-1470109-0
19,200	300	5-1470109-8	1-1470109-8
19,200	300	5-1470109-6	1-1470109-6
22,400	350	5-1470109-4	1-1470109-4
25,600	400	5-1470109-2	1-1470109-2
14,400	450	5-1470109-0	1-1470109-0
17,600	550	4-1470109-8	1470109-8
23,400	650	4-1470109-6	1470109-6

APQ (PCS/CARTON)		PPQ (PCS/BAG)		PART NUMBER		
DIED:	DWN	O. HU 27-JUN-2007		Tyco Electronics Corporation Taipei, Taiwan		
	CHK	S. HOU 27-JUN-2007				
	APVD	W.J. KE 27-JUN-2007		NAME 2.0MM PITCH HEADER, DIP, VERTICAL TYPE		
	PRODUCT SPEC					
	QUALIFICATION TEST REPORT		LOC DW	SIZE A ₃	DRAWING NO C-1470109	REV E
	WEIGHT		SCALE --		SHEET 2 OF 2	

SEE SHEET 1.	ECN	DWN CHK	DATE
LTR	REVISION RECORD		