



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	01/30/04	MCCORMICK
B	ECN 3957: CHANGE MATL HOUSING FROM NYLON TO ABS, NEW FORMAT	4/22/09	D.FRISIELLO
C	ECN 4278: ADDED OPERATING TEMPERATURE RANGE AND PACKAGING	10/1/09	D.FRISIELLO



- NOTES:**
1. RECOMMENDED CABLE DIAMETER: 0.236 ϕ THRU 0.394 ϕ
 2. IP (INGRESS PROTECTION) RATING: 67.
 3. OPERATING TEMPERATURE RANGE: -40°C TO +105°C.
 4. COMPONENT ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.



MATERIALS:

GASKETS: EPDM
BODY: NYLON
HOOSING: ABS
O-RING: SILICONE
SEAL: EPDM
SEALING NUT: NYLON
THUMBSCREW: BRASS

FINISH:

THUMBSCREW: NICKEL PLATE

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] DIMENSIONAL TOLERANCES: .X = ± .1 .XX = ± .02 .XXX = ± .005 ANGULAR TOLERANCES: ALL = ± 1°	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845			
	DRAWN BY C.MCCORMICK	01/28/2004				
	CHECKED BY D.PARHAM	01/28/2004	CATEGORY DATA CABLING			
	APPROVED BY R.CARRICK	01/28/2004	PRODUCT DESCRIPTION DB15 FEMALE WATERPROOF CONNECTOR			
PROJECTION 	COLOR VARIATIONS MAY OCCUR		SIZE A	FSCM NO. 43321	DWG. NO. WPDB15S-KIT	REV. C
			SCALE: NONE		CAD FILE: WPDB15S-KIT.SLDDRW	SHEET 1 OF 1