



HV231-10A High Voltage Probe

Specialty handheld probe

- High voltage probe for AC or DC
- Extended voltage measuring to 40 kV
- Use with standard multimeters with 10 M Ω input impedance

No hassle warranty

No waiting.

No shipping charges.



Our commitment to high-quality products and customer service is demonstrated by our industry exclusive "No Hassle" warranty. In the unlikely event that an Amprobe Test Tool requires warranty service, any of our local dealers are authorized to replace it, on the spot.

(note: \$500 MSLP limit)

Amprobe® Test Tools

website: www.Amprobe.com
email: info@amprobe.com
Everett, WA 98203
Tel: 877-AMPROBE

Amprobe® Test Tools Europe

In den Engematten 14
79286 Glotttetal, Germany
Tel.: +49 (0) 7684 8009 - 0

General Specifications

Operating Temperature	0 °C to 50 °C
Storage Temperature	- 20 °C to 70 °C
Dimensions	340 mm (13.3 in) Length x 30 mm (1 in) Handle x 75 mm (3 in) Guard
Weight	218 g (7.7 oz)
Cable Length	1 m (39 in)

Specifications

Function	Range	Accuracy
Input Resistance	1000 M Ω	
Division Ratio	1000 : 1	
Maximum Working Voltage	40 kV DC or AC peak 28 kV AC RMS	
Accuracy		
HV231-10A	DC V (1 kV to 20 kV)	± 1 %
	DC V (20 kV to 40 kV)	± 2 %
	AC V (1 kV to 20 kV) (50/60 Hz)	± 5 %
Temperature Coefficient	< 200 ppm/°C	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[AMPROBE:](#)

[HV231-10A](#)