



### MATERIALS:

Body: Gold Plated Beryllium Copper,  
Male Contact - Gold Plated Brass,  
Female Contact – Gold Plated Beryllium Copper  
Dielectric: Teflon  
Finish: Body and Contacts – Gold plated  
Marking: "Pomona 4298"

### RATINGS:

Voltage: Shield/Earth: 30VAC/60VDC Max.  
Inner Conductor/Shield: 335VRMS Max.  
Operating Temperature: -65°C (-85°F) to +165°C (+329°F)  
Nominal Impedance: 50 Ohms  
Frequency Range: 0-12.4 GHz.

### ORDERING INFORMATION:

Model 4298

All dimensions are in inches and metric. All specifications are to the latest revisions. Specifications are subject to change without notice.  
Registered trademarks are the property of their respective companies. Made in USA

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[4298](#)