


Series KRPA General Purpose Relays



- Multi-Contact Arrangement

► Octal Plug Termination

► Clear Dust Cover
- Hold-Down Spring for KRPA and KRPA-N Will Accommodate Machine Screws or Rivets; for Use with Flush Mount Chassis Sockets


| U.L. Contact Ratings for KRPA |                                                                               |                                                           |                                                                               |
|-------------------------------|-------------------------------------------------------------------------------|-----------------------------------------------------------|-------------------------------------------------------------------------------|
| Material                      | Silver                                                                        | Silver-Cadmium Oxide                                      |                                                                               |
| Code                          | Y                                                                             | G                                                         |                                                                               |
| Models                        | SPDT, DPDT and 3PDT                                                           | SPDT, DPDT                                                | 3PDT                                                                          |
| Ratings                       | 5 amps @ 120 VAC<br>1/10 HP @ 120 VAC<br>3 amps @ 240 VAC<br>1/6 HP @ 240 VAC | 10 amps @ 250 VAC<br>1/3 HP @ 250 VAC<br>1/6 HP @ 120 VAC | 10 amps @ 120 VAC<br>1/6 HP @ 120 VAC<br>6 amps @ 250 VAC<br>1/3 HP @ 250 VAC |

Ruggedly constructed relay offered with silver contacts, code “Y”, rated 5 amps; and silver-cadmium oxide contacts, code “G” rated 10 amps. Contact arrangements are available up through 3 form (3PDT). Expected life exceeds 100,000 operations at rated load. Mechanical life is 10 million operations, minimum. Enclosed in a clear dust cover. U.L. recognized under file E22575. Low cost version of the KRP relay.

KRPA-N Series has an indicator lamp wired in parallel with its coil, making this model ideal for voltage or current monitoring applications. Silver-cadmium oxide contacts are rated 10 amps. KRPA-N specifications are identical to those of other models in the KRPA series.

| Stock No. | Mfr.'s Type   | EACH  |       |       |
|-----------|---------------|-------|-------|-------|
|           |               | 1-24  | 25-49 | 50-99 |
| 886-0606  | KRPA-5AG-120  | 20.27 | 18.40 | 16.71 |
| 886-0615  | KRPA-11AY-6   | 17.77 | 16.90 | 15.99 |
| 886-0616  | KRPA-11AY-12  | 22.15 | 20.13 | 18.27 |
| 886-0617  | KRPA-11AY-24  | 21.11 | 20.07 | 18.80 |
| 886-0618  | KRPA-11AY-120 | 19.19 | 17.46 | 15.85 |
| 886-0620  | KRPA-11AG-6   | 22.67 | 20.60 | 18.70 |
| 886-0621  | KRPA-11AG-12  | 22.67 | 20.60 | 18.70 |
| 886-0622  | KRPA-11AG-24  | 19.08 | 17.34 | 15.74 |
| 886-0623  | KRPA-11AG-120 | 16.99 | 15.46 | 14.03 |
| 886-0626  | KRPA-11DY-12  | 19.84 | 18.87 | 17.87 |
| 886-0627  | KRPA-11DY-24  | 19.86 | 18.88 | 17.86 |
| 886-0631  | KRPA-11DG-12  | 19.64 | 17.85 | 16.20 |
| 886-0632  | KRPA-11DG-24  | 19.64 | 17.84 | 16.21 |
| 886-0634  | KRPA-11DG-110 | 21.10 | 19.18 | 17.58 |
| 886-0637  | KRPA-14AY-24  | 19.65 | 17.87 | 16.22 |
| 886-0638  | KRPA-14AY-120 | 27.11 | 24.65 | 22.38 |
| 886-0641  | KRPA-14AG-12  | 21.75 | 20.66 | 19.58 |
| 886-0642  | KRPA-14AG-24  | 27.89 | 25.35 | 23.02 |
| 886-0643  | KRPA-14AG-120 | 24.17 | 21.97 | 19.94 |
| 886-0647  | KRPA-14DY-24  | 21.10 | 20.07 | 19.02 |
| 886-0651  | KRPA-14DG-12  | 27.69 | 25.17 | 22.85 |
| 886-0652  | KRPA-14DG-24  | 27.41 | 24.92 | 22.86 |
| 886-0654  | KRPA-14DG-110 | 24.08 | 22.86 | 21.67 |
| 886-0656  | KRPA-11AN-12  | 20.17 | 19.16 | 18.15 |
| 886-0657  | KRPA-11AN-24  | 24.26 | 23.04 | 21.83 |
| 886-0658  | KRPA-11AN-120 | 22.13 | 20.11 | 18.45 |
| 886-0661  | KRPA-11DN-12  | 24.33 | 23.11 | 21.69 |
| 886-0662  | KRPA-11DN-24  | 22.01 | 20.01 | 18.35 |
| 886-0663  | KRPA-11DN-110 | 22.25 | 21.14 | 20.03 |
| 886-0667  | KRPA-14AN-120 | 26.98 | 24.53 | 22.48 |

T9A Series



T9A Series are low cost, printed circuit board or panel mount relays. Up to 30 A switching in SPST and 20 A in SPDT arrangements. Silver-cadmium oxide contacts in 1 Form A (SPST-NO) and 1 Form C (SPDT). Available in unsealed, plastic dust cover (T9AP) or immersion cleanable, sealed plastic case (T9AS). UL Class F insulation system standard. Well suited for various industrial, commercial and residential applications.

| Stock No. | Mfr.'s Type | Volts (DC) | Termination        | Contacts | EACH |       |       |
|-----------|-------------|------------|--------------------|----------|------|-------|-------|
|           |             |            |                    |          | 1-24 | 25-49 | 50-Up |
| 886-2101  | T9AS1D12-12 | 12         | P.C. Mount         | SPST-NO  | 3.10 | 2.74  | 2.48  |
| 886-2102  | T9AS5D12-12 | 12         | P.C. Mount         | SPDT     | 2.66 | 2.29  | 2.09  |
| 886-2103  | T9AS1D12-24 | 24         | P.C. Mount         | SPST-NO  | 3.10 | 2.74  | 2.48  |
| 886-2104  | T9AS5D12-24 | 24         | P.C. Mount         | SPDT     | 2.70 | 2.38  | 2.19  |
| 886-2106  | T9AS1D12-18 | 18         | P.C. Mount         | SPST-NO  | 2.70 | 2.38  | 2.19  |
| 886-2107  | T9AP5D52-12 | 12         | Flange Mount, Q.C. | SPDT     | 3.82 | 3.37  | 3.06  |
| 886-2108  | T9AP5D52-24 | 24         | Flange Mount, Q.C. | SPDT     | 3.81 | 3.38  | 3.06  |
| 886-2109  | T9AS1D22-12 | 12         | P.C. Mount, Q.C.   | SPST-NO  | 3.35 | 2.97  | 2.69  |
| 886-2110  | T9AS1D22-24 | 24         | P.C. Mount, Q.C.   | SPST-NO  | 2.95 | 2.66  | 2.43  |
| 886-2111  | T9AS5D22-12 | 12         | P.C. Mount, Q.C.   | SPDT     | 2.95 | 2.66  | 2.43  |
| 886-2112  | T9AS5D22-24 | 24         | P.C. Mount, Q.C.   | SPDT     | 2.95 | 2.61  | 2.36  |