



QR06 Series


Crossflow Blower

455... 495mm x Ø 88mm 19" Rack Mount Unit

- AC blower with single phase motor. 90° air flow. Ball bearings and terminals. Max ambient temperature of 60 C.
- Fan propeller of aluminium and air duct housing of sheet steel.
- Rotational direction CW looking at rotor.
- Wide, even air flow distribution. "V" shaped guide vane suppresses noise.
- UL, CSA, VDE approvals on some models. Please contact application engineering

19" Rack Mount Unit (Ready for installation) Shipped complete with:	- Capacitor prewired to terminal block - Filter mat and retainer included - Front plate and motor painted black
---	---

Part Number	CFM @ 0	Curve	Volts	Hertz	Power (W)	dBA	Max Ambient Temp C	Wgt. (lbs)	Type Of Bearing	Features	Capacitor (µF)
QR06A-2/106349	190	1	115	50/60	38	55	40	6.00	Ball	Leads	3
QR06A-2/106351	190	1	115	50/60	38	55	40	6.00	Ball	Leads	3
QR06A-2/106350	190	1	230	50/60	41	55	40	6.00	Ball	Leads	1
QR06A-2/106352	190	1	230	50/60	41	55	40	6.00	Ball	Leads	1



PART NUMBER	a	b
QR08A-2/106349	14.96 (380)	18.11 (460)
QR08B-2/106350	14.96 (380)	18.11 (460)
QR08B-2/106351	16.54 (420)	19.69 (500)
QR08B-2/106352	16.54 (420)	19.69 (500)

