


SANYO

Cadnica




Cell Type KR-1400AE

Specifications


Nominal Capacity		1400mAh	
Nominal Voltage		1.2V	
Charging Current	Standard	140mA	
	Fast	2100mA	
Charging Time	Standard	14 to 16Hrs.	
	Fast	about 1Hr.	
Ambient Temperature	Charge	Standard	0°C to +45°C [+32°F to 113°F]
		Fast	0°C to +45°C [+32°F to 113°F]
	Discharge		-20°C to +60°C [-4°F to 140°F]
	Storage		-30°C to +50°C [-22°F to 122°F]
Internal Impedance (Av.) (at 50% discharge)		10.0mΩ (at 1000Hz)	
Weight		31g/1.09oz	
Dimensions(D)×(H) (with tube)		17.0 ⁰ _{-0.5} × 49.5 ⁰ _{-1.2}	mm
		0.67 ⁰ _{-0.02} × 1.95 ⁰ _{-0.05}	inch

Typical Characteristics


Charge




Discharge (at high rate)




Charge



Discharge (at high rate)



Discharge (at low rate)



Temperature (Charge & Discharge)

