











- 1 USE A P.C.B. WHOSE SURFACES ARE TREATED WITH SOLDER RESIST.
- 2 SHOW P.C.B LAYOUT FROM THE CONNECTOR-MOUNTING SURFACE SIDE.
- 3 NUMBER THE CONTACTS IN THE P.C.B OR CONNECTOR CONSECUTIVELY FROM THE BSC SIDE.
- 4 WHEN SCREWING THE CONNECTOR TO THE P.C.B, USE M2 SCREW, NUT AND WASHERS.
- 5 HOUSING MATERIAL : THERMOPLASTICS (UL94-V0). COLOR:BLACK
- 6 CONTACT MATERIAL : COPPER ALLOY
- 7 FINISH : NICKEL 1.27 μ MIN THK. OVERALL SELECTIVE GOLD 0.76 μ MIN THK ON CONTACT AREA AND TIN 1 μ MIN THK ON TINE AREA.

6-	-8	96	47	59.69	65.66	69.66	73.66
6-	-6	48	23	29.21	35.18	39.18	43.18
6-	-5	34	16	20.32	26.29	30.29	34.29
6-	-4	60	29	36.83	42.80	46.80	50.80
6-	-3	50	24	30.48	36.45	40.45	44.45
6-	-2	40	19	24.13	30.10	34.10	38.10
6-5173280-1		30	14	17.78	23.75	27.75	31.75
P/N		POS	n	A	B	C	D

THIS DRAWING IS A CONTROLLED DOCUMENT.

0	PLC	$\pm -$
1	PLC	$\pm -$
2	PLC	$\pm -$
3	PLC	$\pm -$
4	PLC	$\pm -$
ANGLES		$\pm -$

MATERIAL
材料 SEE - 5 6
参照

FINISH
仕上 SEE 
参照 - 7

DWN	—
CHK	—
APVD	—
PRODUCT SPEC	製品規格
APPLICATION SPEC	取付適用規格
WEIGHT	

CUSTOMER DRAWING



TE Connectivity

NAME 名称	CAP ASSY VERTICAL AMPLIMITE .050 SERIES I B-TO-B CONN.
------------	---

SIZE	CAGE CODE	DRAWING NO 番号	RESTRICTED TO
A3	00779	C-5173280	—

SCALE 比例	2:1	SHEET 张数	3 OF 3	REV 修改	A2
-------------	-----	-------------	--------	-----------	----