



WCB40

WEJTAP CONN BLU

ACTIVE



Electrical division

☒ [Email Datasheet](#) [Print Datasheet](#)

FCI Brings You More

☒ [Contact our sales/technical support](#)

☒ [Sample request](#)

€ [Price request](#)

Download document

Literature

- [> Wejtap Material Safety Data Sheet - Power Cell](#)
- [> Wejtap Material Safety Data Sheet - Black Powder Solvent](#)
- [> Wejtap Product Focus](#)
- [> Wejtap Brochures](#)
- [> Connector Theory and Application Brochure](#)

Application Tooling

- [> Electrical Tooling](#)

Specifications

Dimensional	Physical	Approvals / Certifications	Other Features
Dimensional			
Conductor Size (Run - Diameter)	0.603 to 0.684		
Conductor size (Run - Max)	336.4-18/1		
Conductor size (Run - Min)	3364		
Conductor Size (Run - mm)	15 mm² to 17 mm²		
Conductor Size (Run)	336.4 336.4-18/1		
Conductor size (Tap - Max)	#6-6/1		
Conductor size (Tap - Min)	#6		
Conductor Size (Tap)	#6-6/1 #6		
Conductor Type (Run)	AAC ACSR		
Wire Size	AWG		
Wire Size (Tap - Diameter - in)	0.162 to 0.204		
Wire Size (Tap - mm)	4 mm² to 5 mm²		
Wire Type (Tap)	ACSR AAC Copper		
Physical			
Color Code	Blue		
Approvals / Certifications			
UL Listed	No		
CSA Certified	No		
Other Features			
Installation Tool	WTRB		
Booster	WPBB Box 25		
UPC	78181087340		
Keyw ord	w ejtap		