

Heat gun GHG 660 LCD Professional



**Heat gun
GHG 660 LCD
Professional**

The heat gun with the
greatest ease of use

Technical data

Rated power input 2.300 W

Weight 1,0 kg

Height 255 mm

Specifications, use

Working temperature 50 – 660 °C

Airflow 250 – 500 l/min

Infinitely variable
temperature control X

Cold-air setting, 50°C X

Control, airflow infinitely variable

Functions

Part number

0 601 944 742