



RIA US



RIA US

ATW03E

Tubular screw terminal block, centerline 12 mm / 0.472 inches, 1.2 mm / 0.047 inches raised base, horizontal wire entry

Technical Data

RIA US V / A / AWG	300 / 35 / 22 - 10
Screw torque	max. 7 lbs.-in
Screw torque	max. 0.8 Nm
Wire strip length	7.8 mm / 0.307 in.
Pole size	1 to 12
Color	Natural

ATW04E


Tubular screw terminal block, centerline 12 mm / 0.472 inches, 1.2 mm / 0.047 inches raised base, horizontal wire entry, wire protector

Technical Data

RIA US V / A / AWG	300 / 35 / 22 - 10
Screw torque	max. 7 lbs.-in
Screw torque	max. 0.8 Nm
Wire strip length	7.8 mm / 0.307 in.
Pole size	1 to 12
Color	Natural

Dimensions in mm

1 mm = 0.0394 in.



	A	B	C	D	E	F
mm	140.7	23.8	19.0	12.0	3.9	3.9±0.1
inches	5.540	0.937	0.748	0.472	0.154	0.154

L = (PS-1)12+8.7 mm

Part numbers (P/N)

(information: page 165)

Complete the part number by adding the pole size.

ATW03E

centerline 12 mm / 0.472 inches

P/N ATW03E


	01	02	03	04	05	06	07	08
	09	10	11	12				

Standard pole sizes

Available on demand. Minimum order quantity 5000 pieces per item.

Dimensions in mm

1 mm = 0.0394 in.



	A	B	C	D	E	F
mm	140.7	23.8	19.0	12.0	3.9	3.9±0.1
inches	5.540	0.937	0.748	0.472	0.154	0.154

L = (PS-1)12+8.7 mm

Part numbers (P/N)

(information: page 165)

Complete the part number by adding the pole size.

ATW04E

centerline 12 mm / 0.472 inches

P/N ATW04E

	01	02	03	04	05	06	07	08
	09	10	11	12				

Standard pole sizes

Available on demand. Minimum order quantity 5000 pieces per item.