





Mating Height Draw.



Pos	A	B	C	Pos	A	B	C
4	7.00	3.81	5.60	16	22.24	19.05	20.84
6	9.54	6.35	8.14	18	24.78	21.59	23.38
8	12.08	8.89	10.68	20	27.32	24.13	25.92
10	14.62	11.43	13.22	22	29.86	26.67	28.46
12	17.16	13.97	15.76	24	32.40	29.21	31.00
14	19.70	16.51	18.30	26	34.94	31.75	33.54

Specifications:

Current rating:1.5A AC,DC

Voltage rating:230V AC, DC

Contact resistance:20m ohm. Max.

Insulation resistance:1000M ohm. Min.

Withstanding voltage:AC 500V AC/minute

Operating temperature range:-40°C ~ +105°C

Materials:

Insulator:High Temp. Plastic (UL94V-0)

Contact material:Phosphor Bronze

Finish:Tin Plated

How to Order

TMM-X-X-XX-X

Type

- 1-IDC Male
- 2-IDC Plug
- 3-DIP Male Straight
- 4-DIP Female Straight
- 5-DIP Female R/A
- 6-SMT Female Straight


Packaging

- 1 - Tape & Reel with vacuum cap
- 2 - Tube
- 3 - Bag
- 4 - Tape & Reel without vacuum cap

Number of Positions
04, 06, 08, 10, 12, 14,
16, 18, 20, 22, 24 or 26

Locking System

- 0-without lock
- L-with lock



PCB Layout



TOLERANCE (mm)	APPROVALS	DATE	TITLE	AMPHENOL
X. ±0.3	DRAWN Stephane	2009/10/07	TMM Series	Amphenol European Design Center
X.X ±0.2	CHECKED Rob	2009/10/07	R/A Dip Female	
X.XX ±0.15	APPROVED Rob	2009/10/07		
UNLESS OTHERWISE SPECIFIED	UNIT:	SIZE: A4	DRAWING N° TMM-5-0-XX-X	Scale N.A. Sheet 1 of 1
				REV. D