

Olympic Wire and Cable

7 Madison Road • Fairfield, NJ 07004

973.227.7996 800.526.2269 • Fax: 973.227.1606

email: sales@olympicwire.com

Olympic P/N 366, UL LISTED UL1015, UL1032, UL1230**UL LISTED UL1015, UL1032, UL1230**

Stranded Tinned Copper, Color Coded PVC Insulation.

Characteristics:

Temperature Rating — 40°C to +105°C

Resistant to acids, alkalis, oil, flame, moisture and fungus

SPECIFICATIONS

Conductor Size	12 AWG
Stranding	65/30 Tinned Copper
Insulation	PVC
Nom. Wall Thickness	0.031 in
Nom. O.D.	0.158 in
UL Style	1015 1032 1230 MTW
UL Rating	600 V, 90°C, 1000 V
UL Flame Test	VW-1
CSA Type	TEW
CSA Flame Test	FT-1
Boat Cable	BC-5W2
Operating Temperature	-40 to +105 °C
RoHS Compliant	 RoHS Compliant
Color Code	Hook Up Wire Color Code Chart