


DC Power Jack




163-2640-E, 163-2641-E

KOBICONN

DC Power Jack



RECOMMENDED P.C.B LAYOUT (COMPONENT SIDE)
P.C.B. THICKNESS = 1.20mm



P/N	PIN DIM.
163-2640-E	2.00±.05
163-2641-E	2.45±.05

Dimensions: mm

MATERIAL SPECIFICATIONS

1	Housing: High Temp. Plastic
2	Terminal: Copper Alloy
3	Terminal Plating: Silver on Contact and Solder Al Over Nickel
4	Center Pin: Copper Alloy
5	Center Pin Plating: Nickel
RoHS Compliant by Exemption	

Date Last Revised: 6/13/12

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC-301316

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

163-2640-E, 163-2641-E

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[163-2640-E](#) [163-2641-E](#)