


Technical datasheet: KPX-G0901B-K6333

Specifications:

Operating Temperature	-20°C to +70°C
Storage Temperature	-30°C to +80°C
Rated Voltage	1.5VDC
Operating Voltage	1VDC to 2VDC
Max. Rated Current	15mA at 1.5VDC
Resonant Frequency	2.7kHz \pm 0.3kHz
Min SPL	70dB/ 1.5VDC/ 10cm
Weight	1g
Case Material/Color	PBT/Black
Tone Nature	Continuous

Dimensions:



Frequency Response:

