

JR3050T RECIPROCATING SAW



PRODUCT DESCRIPTION

Can be used for:

Cutting sheet, pallets, wood with nails, plastic, cast iron pipe.

Remedial work.

Window replacement.

Pruning and brush cutting.

Standard Equipment

Recipro blades.

Max. Cut In Pipe: 90mm

Max. Cut In Wood: 90mm

Length Of Stroke: 28mm

Strokes Per Minute: 0-2,800spm

Orbital Action: No

Input Wattage: 1,010w

Net Weight: 3.2kg