




Pos. 16

C4

Pos. 24

C3

DETAIL A

Pos. 17

Pos. 1

Pos. 9

C5

Pos. 8

C2

C1

P1

2

3

4

Hood, White(WH03)

5

4

1

Length (See Table)

4

5

Hood, White(WH03)

4

3

2

Pos. 9

Pos. 1

Pos. 17

Pos. 16

Pos. 24

C1

C2

C3

C4

C5

P2

CKT 14

SIDE VIEW OF DETAIL A

BACK SIDE

PIN ASSIGNMENT :

P1

1

2

3

6

7

8

9

10

11

14

15

16

17

18

Pair.1

Drain (Pair.1)

Pair.

Pair.2

Drain (Pair.2)

Pair.3

P2

1

2

3

6

7

8

9

10

11

14

15

16

17

18

P1

19

23

24

22

C1

C5

C2

C5

C3

C5

C4

Shell

Drain (Pair.3)

Pair.4

Drain (Pair.4)

Coaxi. Red

Coaxi. Red

Coaxi. Gray

Coaxi. Gray

Coaxi. Blue

Coaxi. Blue

Outer Braid

P2

19

23

24

22

C1

C5

C2

C5

C3

C5

C4

Shell

NOTE :

Cable Assembly Must Pass DVI 1.0 Specification.

3000±80		1653929-3
2000±60		1653929-2
1000±30		1653929-1
LENGTH(L)	CUSTOMER P/N	TYCO P/N

Thumbscrew,DVI, #4-40, 3*45mm

5

PVC, Shore A 90-95, Color: White (WH03).

4

Metal Can For DVI Connector, Meet OD: 9.5mm

3

Connector, DVI-I, Gold 30U"Plated

2

UL20276 [30AWG*3Coax.+(28AWG*1P+Drain+Al/Mylar

1

*4+28AWG*1P+28AWG*6C]+Al/Mylar+Braid, Black(BK01)

DESCRIPTION

ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± -
FINISH	-

MATERIAL

-

DWN

JURRY LIU

22/JAN/03

CHK

-

APVD

OZ

02/SEP/03

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING

tyco

Electronics

Tyco Electronics Corporation

Harrisburg, Pa 17105-3608

NAME

CABLE ASSY, DVI-1 TO DVI-1

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=1653929

-

SCALE

N.T.S

SHEET

1

OF

1

REV

A1

AMP 1470-19 REV 31MAR2000