







NOTES:
MATERIAL:
CONTACTS:BRASS T=0.25mm
INSULATOR:PTI+30%G.F. UL 94V-0
FRONT SHELL:BRASS T=0.30mm
BACK SHELL:SPCC T=0.30mm
SPRING:SPCC
MECHANICAL:
MATING:35N MA
WITHDRAWAL FORCE:10N MIN
DURABILITY:1500CYCLES MIN
ELECTRICAL:
CURRENT RATING:1.5A
VOLTAGE RATING:30V
WITHSTANDING VOLTAGE:750V AC
CONTACT RESISTANCE:25mΩ MAX
INSULATION RESISTANCE:1000MΩ MIN
PLATING
CONTACTS:GOLD FLASH AND TIN OVER NICKEL PLATED
SHELL:NICKEL OVER ALL PLATING
ENVIRONMENTAL:
TEMPERATURE RANGE:-55℃XC TO+85℃XC



P.C.B LAYOUT

10/01/30			ING		EG-N1012072				A3								
09/12/29			BENDEE		EG-H12067		變更尺寸標注位置		A2								
DATE			DR.BY		ECN.NO.		DESCRIPTION		MARK		VER.						
-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差參考表					CnC Tech,LLC												
X.X			±0.38		X.X°		±2.0°		APPD:			  TITLE: USB 8P A/F 雙層DIP 90°雙彈片30U"成品					
X.XX			±0.25		X.XX°		±1.0°		CHECK:								
X.XXX			±0.13		X.XXX°		±0.5°		DRAW:								
					PRODUCT NO: 1002-004-01010			DATE		SCALE		UNIT		TYPE		PAGE	
								2010.01.30		1:1		mm		CD		1 / 1	