

10 outlet, 8-ft cord, 3345 joules, Tel/Modem and Coaxial protection - Protect It! Surge Suppressor

MODEL NUMBER: TLP1008TELV



Description

Tripp Lite's TLP1008TELV offers economical AC surge suppression for protection of workstations, PCs, telecom systems, home electronics and other sensitive equipment. The TLP1008TELV features 10 outlets, an 8-ft. cord with a space-saving right-angle plug, and diagnostic LEDs to warn of suppressor damage. The unit has a surge suppression rating of 3345 joules to shield equipment from line noise and the strongest surges. Built-in RJ11 jacks prevent surges from damaging your modem/fax/phone equipment. Built-in 2.2GHz goldcoax jacks prevent surges from damaging your cable/satellite equipment. \$150,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

PLUG/OUTLETS: Input: NEMA5-15P/Output: 10 NEMA5-15R/8-ft. AC line cord

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA5-15R wall receptacle)

FORMAT: Corded multi-outlet strip with 5 transformer-spaced outlet

SUPPRESSION: AC: 150V RMS Clamping/3345 joules/400V UL1449 3rd Edition

Features

- 10 outlets with child safety covers
- 8-ft. cord with space-saving right-angle plug
- Built-in RJ11 jacks prevent surges from damaging your modem/fax/phone equipment; - built-in splitter protects two devices sharing a single line; 6-ft. telephone cord included
- Built-in 2.2GHz gold coax jacks prevent surges from damaging your cable/satellite equipment; 6-ft gold coax cable included
- Surge suppression rating: 3345 joule protection
- EMI/RFI noise filtering
- 15 amp resettable circuit breaker
- Diagnostic LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
- Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
- Can accommodate up to 4 transformers without blocking remaining outlets
- Keyhole supports for wall mounting
- \$150,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only) covers connected equipment

Highlights

- 10 outlets / 8-ft. cord
- 1 in/2 out tel/modem surge protection
- 1 line 2.2GHz gold coaxial protection
- 3345 joule rating
- \$150,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Applications

- Ideal for protecting TVs, DVDs, satellites, stereos and other entertainment systems

Package Includes

- TLP1008TELV surge suppressor
- 6-ft. RJ11 cable
- 6-ft gold coax cable
- Instruction manual and warranty information



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- Failsafe shutdown mode
- Lighted power switch

Specifications

| OVERVIEW | |
|------------------------------------|--|
| Intended Application | Home/Office; Audio/Video |
| Style | Strip |
| OUTPUT | |
| Frequency Compatibility | 50 / 60 Hz |
| Output (Watts) | 1800 |
| Circuit Breaker (amps) | 15 |
| Overload Protection | 15A resettable circuit breaker |
| Outlet Quantity / Type | 10 NEMA 5-15R |
| Number of Outlets | 10 |
| Transformer Accommodation | Supports 4 large transformer plug accessories without covering remaining outlets, accepts up to 8 transformers total |
| Outlet Safety Covers | Includes built-in sliding outlet safety covers |
| Outlet Orientation | Two rows of outlets, including 4 widely spaced for transformers |
| INPUT | |
| Nominal Input Voltage(s) Supported | 120V AC |
| Recommended Electrical Service | 120V (110-125V) |
| Input Connection Type | NEMA 5-15P |
| Input Plug Features | Space-saving right angle input plug |
| Input Cord Length (ft.) | 8 |
| Input Cord Length (m) | 2.4 |
| Input Cord Gauge Type | 14 gauge, SJT |
| Voltage Compatibility (VAC) | 120 |
| Maximum Surge Amps | 135000 |
| LEDS ALARMS & SWITCHES | |
| Switches | Two-position on/off power switch |
| Diagnostic LEDs | Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status |
| SURGE / NOISE SUPPRESSION | |
| AC Suppression Joule Rating | 3345 |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|------------------------------|--|
| AC Suppression Response Time | < 1 ns |
| Protection Modes | Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression |
| Clamping Voltage (RMS) | 150V |
| UL1449 Let Through Rating | 400V - UL Verified |
| EMI / RFI Filtering | Up to 40dB |

DATALINE SURGE SUPPRESSION

| | |
|----------------------------------|--------|
| Telephone/DSL Protection | Yes |
| Telephone/DSL Protection Details | 1 line |
| Cable (Coax) Protection | Yes |
| Cable (Coax) Protection Details | 1 line |
| Network (Ethernet) Protection | No |

PHYSICAL

| | |
|--|--|
| Shipping Dimensions (hwd / in.) | 14.75 x 7.75 x 2.3 |
| Shipping Dimensions (hwd / cm) | 37.5 x 19.7 x 5.8 |
| Unit Dimensions (hwd / in.) | 11.6 x 5 x 2.25 |
| Unit Dimensions (hwd / cm) | 29.5 x 12.7 x 6.5 |
| Unit Weight (lbs.) | 2.2 |
| Unit Weight (kg) | 1.0 |
| Material of Construction | Plastic |
| Integrated Keyhole Mounting Tabs | Keyhole mounting tabs enable wall mounting |
| Housing Color | Black |
| Receptacle Color | Black |
| Color (AC Line Cord) | Black |
| Outlets Measurement (Center to Center) | Between Standard Outlets = 28.4mm; Between Standard and Transformer Outlets = 56.8mm |
| Keyhole Slot Mounting Measurement (Center to Center) | 108mm |

SPECIAL FEATURES

| | |
|------------------|-----|
| Right-Angle Plug | Yes |
|------------------|-----|

CERTIFICATIONS

| | |
|-------------------------------------|--------------------|
| UL1449 3rd Edition (AC Suppression) | UL1449 3rd Edition |
| UL1363 (Power Tap) | UL1363 |
| UL497A (Communications) | UL497A |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|--|---|
| FCC Part 68 (Communications) | FCC Part 68 |
| cUL / CSA (Canada) | cUL |
| Industry Canada (Communications) | Industry Canada |
| Approvals | Exceeds IEEE 587 category A&B specifications |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |
| Connected Equipment Insurance (U.S., Canada & Puerto Rico) | \$150,000 Ultimate Lifetime Insurance |

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.