


Metric countersunk head machine screws - Slotted



DIN 963
BS 4183
ISO 2009

Materials/Finishes:

Steel 4.8/Zinc & clear
Stainless steel/Self colour
Brass/Self colour

Dimensions

Thread (d)	M2	M2.5	M3	M3.5	M4	M5	M6	M8
H max (BS/DIN)	1.2	1.5	1.65	1.93	2.2	2.5	3	4
H max (ISO)	1.2	1.6	1.65	2.35	2.7	2.7	3.3	4.65
D nom (DIN)	3.8	4.7	5.6	6.5	7.5	9.2	11	14.5
D nom (BS)	4.4	5.5	6.3	7.35	8.4	10	12	16
D nom (ISO)	3.8	4.7	5.6	7.3	8.4	9.3	11.3	15.8
w (slot width) nom	0.6	0.7	0.9	1	1.3	1.3	1.7	2
t (slot depth) min	0.8	1	1.2	1.4	1.6	2	2.4	3.2

NB: Generally our preferred stock is to DIN - if dimensions are critical to your application you should check with us prior to ordering.

Preferred lengths

		Thread (d)							
		M2	M2.5	M3	M3.5	M4	M5	M6	M8
Length (L)	4								
	5	ST	ST	ST					
	6	ST	ST	ST BR		ST BR			
	8	ST	ST	ST BR		ST BR	ST		
	10	ST	ST	ST BR		ST BR	ST BR	ST	
	12	ST	ST	ST BR		ST BR	ST BR	ST BR	ST
	16	ST		ST BR		ST BR	ST BR	ST BR	ST
	20	ST		ST BR		ST BR	ST BR	ST BR	ST
	25			ST BR		ST BR	ST BR	ST BR	ST
	30			BR		ST BR	ST BR	ST BR	ST

	35						ST	ST BR	ST
	40						ST	ST BR	ST
	45								ST
	50								ST
	60								ST
	65								ST
	70								ST

ST - Steel, Zinc & clear - other finishes often available
BR - Brass, Self colour