




Transformer No.	MT 0100SS	1 -Phase / -con.	50 Hz.
Customer	MEDICAL STANDARD	Note	
Assembly comp.	MOUNTING DISK DIAM. 70 mm	Date/sign.	11-01-1991 CK (2)

THERMAL FUSE THERMIK S01 110°C



THERMAL FUSE THERMIK S01 110°C



SCREEN --- GREEN/YELLOW ---
0.006" thick



Marking



MADE BY AMVECO MAGNETICS USA TRF# MT 0100SS



TEMP. PROT. TYPE THERMIK S01 110 C
PRIM. 2*(0-100-120V) 50/60Hz 114VA
SEC. 120V 100VA

Changed from

Changed to

Tests.	Uo. Tolerance, ± 3 %	Iomax: 27.8 (mA)	100 V over P1.	Isol: 4K v
--------	----------------------	------------------	----------------	------------

Dimensions:	Max H: 2.1" (inch)	Max. Ø: 4.2" (inch)	Terminals: MIN 250 mm
-------------	--------------------	---------------------	-----------------------

Max leakage current 50 uA

- 1 PC METAL DISK ø 70 mm
- 2 PCS RUBBER GASKETS ø 70 mm

SHIPPING WEIGHT: 2.80 lbs T

