

Specification Sheet

Part Number: 161-63403



Unique open design allows for easy branch-offs at any point along the harness.

Overwrap formation provides abrasion protection and accommodates multiple bundle configurations.

Flexible construction and design is well suited for applications that involve movement and vibration.

Easy to use installation tool makes assembly fast and easy.

Helawrap, HWPAV025, 1" (25mm) Dia, PA6V0, Black, 100 ft/reel

Article Number	161-63403
Type	HWPAV025
Color	Black (BK)
Quantity Per	pack
Product Description	The Helawrap cable management system is the flexible routing and protection solution for industrial, datacom and electrical applications. Helawrap easily wraps around cables with a "zipper-like" motion to protect against abrasion and mechanical stress caused by movement and bending. A handy application tool is included in every package for faster installations.
Short Description	Helawrap, HWPAV025, 1" (25mm) Dia, PA6V0, Black, 100 ft/reel

Global Part Name	HWPAV025-PA6V0-BK
------------------	-------------------

Length L (Imperial)	100.0
---------------------	-------

Length L (Metric)	30.48
-------------------	-------

Variant	Spiral Binding
---------	----------------

Bundle Diameter Min (Imperial)	0.91
--------------------------------	------

Bundle Diameter Min (Metric)	23.0
------------------------------	------

Bundle Diameter Max (Imperial)	1.06
--------------------------------	------

Bundle Diameter Max (Metric)	27.0
------------------------------	------

Diameter D (Imperial)	1.0
-----------------------	-----

Diameter D (Metric)	25.0
---------------------	------

Nominal Diameter (Imperial)	1
-----------------------------	---

Nominal Diameter (Metric)	25.0
---------------------------	------

Wall Thickness WT (Imperial)	0.041
------------------------------	-------

Wall Thickness WT (Metric)	1.05
----------------------------	------

Material	Polyamide 6 V0 (PA6V0)
----------	------------------------

Material Shortcut	PA6V0
Flammability	UL 94 V-0
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +194°F (-40°C to +90°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL UL 1441 EN [45545-2]
UL Recognized (US)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	30.48
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com