



Metal Working Tools - Small Angle Grinders - 115mm DEWALT SAG

D28117



D28117 Features

- The electronic variable speed control offers added tool control and enables the tool to be used at optimum conditions to suit the accessory and material
- No volt release switch will prevent the unit starting when plugged in, even if the switch is in the on position. Switch must be consciously reset before power is delivered
- Autobalancer reduces vibration resulting in greater comfort
- Overload protection will prevent the unit overheating by shutting the unit off until the unit has cooled down
- Torque limiting clutch reduces the maximum torque reaction transmitted to the operator if the cutting disc jams
- Dust ejection system removes majority of debris from the air which passes over the motor, preventing abrasion and tracking
- Anti vibration side handle to improve user comfort
- New guard design allows guard adjustment without the use of tools, for increased flexibility
- Fully leaded stator windings for increased motor durability
- Pop off brushes protect the armature from damage at the end of brush life resulting in greater motor durability
- Small girth allows comfortable gripping resulting in superior ergonomics
- The low profile gearcase allows access in confined areas
- Abrasion protected motor for increased motor durability
- Anti lock flange prevents flanges from permanently locking up and locking the disc on
- One piece brush arm prevents brush hang up in extreme conditions
- Side positioned spindle lock gives greater protection to button when using in confined spaces

D28117 Specifications

Power Input	1100 Watts
No Load Speed	2800 - 10000 rpm
Max. Disc Diameter	115 mm
Spindle Thread	M14
Weight	2.5 kg
Length	315 mm
Height	90 mm

D28117 Standard

- Protective keyless guard
- Multi position anti vibration side handle
- Inner and outer disc flanges
- Spanner