


JKL PART NUMBER	LENGTH A +/- 2mm	COLOR 5200° KELVIN	STARTING CIRCUIT VOLTAGE VS (Vrms)	OPERATING LAMP VOLTAGE VL (Vrms)	OPERATING LAMP CURRENT IL (mA rms)	BRIGHTNESS (CANDELA/m2)	*RATED LIFE (HRS)
BF8300-20A	300mm	LCD HIGH OUTPUT WHITE	1200	390	5 ± 1	4,000	20,000

* NOTE: RATED LIFE IS DEFINED AS THE POINT AT WHICH THE INTENSITY BECOMES 50% OF THE INITIAL RATING.

METRIC  THIRD ANGLE PROJECTION	DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0 ANGLE +/- 0	JKL COMPONENTS CORPORATION					
	DRAWN BY L. WENGSTROM	APPV'D BY J.K.	DATE 8/12/03	SIZE A	FSCM NO. 55335	DRAWING NO. BF8300-20A	
- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED			SCALE NONE	RELEASED DATE 8/12/03	REVISION DATE	REV. NO.	SHEET 1 OF 1

REV. NO.	RELEASED	8/12/03	APPV'D DATE
	DESCRIPTION/ECO NUMBER		